

Run & Start Capacitor Terminal Covers



2MEU9, 2MEV1, 5AGK8, 12N982, 12N983, 12N984 & 12N985

REV.
0

Run & Start Capacitor Terminal Covers & Guards



Note: Capacitor dimensions to measure are shown by blue or green arrows as referenced below.

Capacitor Accessory Type	Maximum Capacitor Width Dimension	SKU
	Plastic Capacitor Terminal Guard One hole top-side center (yellow arrow). Fits oval capacitors 2" wide by 1-1/4" deep. (use green arrow above as the dimension reference)	2MEU9
	One slot on top (yellow arrow) of rubber cover. Fits oval capacitors 2" wide by 1-1/4" deep. (use green arrow above for the metal bracket dimension) Fits capacitors with terminal widths up to 1-1/2" wide. (use blue arrow above for the rubber cover dimension)	2MEV1

Dayton Electric Mfg. Co. Lake Forest, IL 60045 USA

Run & Start Capacitor Terminal Covers

2MEU9, 2MEV1, 5AGK8, 12N982, 12N983, 12N984 & 12N985			REV. 0
	<p>One hole on side (yellow arrow) of rubber cover. Fits capacitors with terminal widths up to 1-1/2" wide. (use blue arrow above as the dimension reference)</p>	<p>12N982</p>	
	<p>One slot on top (yellow arrow) of rubber cover. Fits capacitors with terminal widths up to 1-1/2" wide. (use blue arrow above as the dimension reference)</p>	<p>12N983</p>	
	<p>Two holes on top (yellow arrows) of rubber cover. Fits capacitors with terminal widths up to 1-1/2" wide. (use blue arrow above as the dimension reference)</p>	<p>12N984</p>	
	<p>Three holes on side (yellow arrows) of rubber cover. Fits capacitors with terminal widths up to 2-3/8" wide. (use blue arrow above as the dimension reference)</p>	<p>12N985</p>	
	<p>One hole on top (yellow arrow) of rubber cover. Round Capacitor Rubber Boot. Fits round capacitors 1-3.4" diameter. (use blue arrow above as the dimension reference)</p>	<p>5AGK8</p>	