



LINEAR LOW CAN LINERS

The linear low density polyethylene in these trash bags helps to add film strength and tear resistance against sharp objects under rough transport conditions. The bags are suitable for disposing of broken and shattered glass or plastic. Linear low-density polyethylene liners are manufactured with high-quality, LLDPE resins, which help to add film strength and tear resistance against sharp objects under rough transport conditions. The coreless roll put-up makes handling and inventory control easy.



- Top quality resins
- Maximum film strength
- Puncture and tear resistant
- Leak-resistant star seal
- Wide range of strengths and sizes
- Packed for easy stacking and storage
- Available on coreless rolls

Can/Liner Compatibility Chart

10 Gallon 31DL10	15 Gallon 15E454	16 Gallon 15E453	23 Gallon 15E455	20-30 Gallon 5XL54 31DK41 31DK67 4YPA2 1LYL9 31DK48	30 Gallon 31DK68	32 Gallon 15E456
33 Gallon 31DK70 1YLZ1 31DK34 4YPA4 5XL55 31DK49 31DK42	42 Gallon 5AU51	40-45 Gallon 31DK73 31DK43 31DK74 31DK75 31DK35 5XL58 5XL57 31DK46 5XL64 4YPA6 31DK50		44 Gallon 5XL56 15E457 31DK76 15E458	50 Gallon 31DK77	54 Gallon 31DK78 31DL09
55 Gallon 31DK79 5XL62 31DK37 15E459 5XL61 4YPA8 4YPA1 31DK40		56 Gallon 31DK80 31DK44 31DK36 5XL60 5XL59 15E460 31DK51 4YPC1 31DK81		60 Gallon 31DK82 5XL63 31DK38 31DK84 5XL65 31DK45 31DK83 31DK47 31DK39 4YPC3 31DK52		

(See reverse for product specifics)

Call or visit your local branch or go to grainger.com/toughguy for complete product line information.

©2019 W.W. Grainger, Inc. W-BUPX115-01



Linear Low - Coreless Rolls

Item No.	Gallon Capacity	Size	Gauge Mils	Max Load	Color	Case Pack	Liners/ Roll	Rolls/ Case
31DK63	7	20 x 21	0.35	15	Black	1000	50	20
31DK64	7-10	24 x 23	0.35	15	Black	500	50	10
31DK31	7-10	24 x 23	0.35	15	Clear	1000	50	20
5XL52	7-10	24 x 23	0.40	20	Gray	500	50	10
31DL10	10	24 x 26	0.75	55	Clear	250	25	10
31DK65	10-15	24 x 32	0.35	15	Black	500	50	10
31DK30	10-15	24 x 32	0.35	15	Clear	500	50	10
5XL53	10-15	24 x 32	0.40	20	Gray	500	50	10
15E454	15	23.5 x 43	0.75	60	Clear	250	25	10
15E453	16	23 x 31	0.59	45	Clear	500	25	20
15E455	23	26.5 x 45	0.75	60	Clear	250	25	10
31DK66	20-30	30 x 36	0.45	30	Black	250	25	10
31DK32	20-30	30 x 36	0.45	30	Clear	250	25	10
5XL54	20-30	30 x 36	0.50	35	Gray	250	25	10
31DK67	20-30	30 x 36	0.60	40	Black	250	25	10
1YL9	20-30	30 x 36	0.70	50	Gray	250	25	10
31DK48	20-30	30 x 36	1.00	65	White	200	25	8
31DK41	20-30	30 x 36	1.00	65	Clear	200	25	8
4YPA2	20-30	30 x 36	1.00	75	Gray	100	10	10
31DK68	30	26 x 43	1.10	70	Black	100	10	10
15E456	32	33 x 44	0.98	70	Clear	200	20	10
31DK33	33	33 x 39	0.45	30	Clear	250	25	10
31DK69	33	33 x 39	0.45	30	Black	250	25	10
31DK70	33	33 x 39	0.60	40	Black	250	25	10
31DK34	33	33 x 39	0.60	40	Clear	250	25	10
5XL55	33	33 x 39	0.70	50	Gray	250	25	10
31DK71	33	33 x 39	0.80	55	Black	250	25	10
31DK49	33	33 x 39	1.00	65	White	150	15	10
31DK42	33	33 x 39	1.10	70	Clear	200	25	8
1YLZ1	33	33 x 39	1.00	65	Gray	200	20	10
4YPA3	33	33 x 39	1.50	90	Gray	100	20	5
4YPA4	33	33 x 39	2.00	110	Gray	100	10	10
31DK72	38	30 x 46	0.80	55	Black	100	10	10
5AU51	42	33 x 48	3.00	120	Black	120	20	6
31DK73	40-45	40 x 46	0.50	35	Black	250	25	10
31DK74	40-45	40 x 46	0.65	45	Black	125	25	5
31DK35	40-45	40 x 46	0.65	45	Clear	125	25	5
5XL57	40-45	40 x 46	0.70	50	Gray	125	25	5
5XL64	40-45	40 x 46	0.90	60	Gray	150	25	6
31DK50	40-45	40 x 46	1.00	65	White	100	10	10
31DK43	40-45	40 x 46	1.10	70	Clear	100	10	10
31DK75	40-45	40 x 46	1.10	70	Black	100	10	10

Item No.	Gallon Capacity	Size	Gauge Mils	Max Load	Color	Case Pack	Liners/ Roll	Rolls/ Case
5XL58	40-45	40 x 46	1.10	75	Gray	100	10	10
4YPA5	40-45	40 x 46	1.50	90	Gray	100	20	5
31DK46	40-45	40 x 46	1.70	90	Clear	100	10	10
4YPA6	40-45	40 x 46	2.00	110	Gray	100	10	10
5XL56	44	36 x 50	0.70	50	Gray	100	10	10
15E457	44	36.5 x 50	0.98	70	Clear	150	15	10
31DK76	44	36 x 46	1.10	70	Black	100	10	10
15E458	44	36.5 x 50	1.20	85	Clear	150	15	10
31DK77	50	45 x 47	1.20	75	Black	100	10	10
31DK78	54	50 x 43.5	1.10	70	Black	100	10	10
31DL09	54	50 x 43.5	1.10	70	Clear	100	10	10
31DK79	55	36 x 58	0.70	50	Black	100	10	10
31DK37	55	36 x 58	0.70	50	Clear	100	10	10
5XL61	55	36 x 58	0.70	50	Gray	100	10	10
4YPA1	55	41 x 54	0.90	80	Gray	100	25	4
31DK40	55	36 x 58	1.00	70	Clear	100	10	10
5XL62	55	36 x 58	1.10	75	Gray	100	10	10
15E459	55	39.5 x 53	1.20	85	Clear	100	10	10
4YPA7	55	36 x 58	1.50	90	Gray	100	20	5
4YPA8	55	36 x 58	2.00	110	Gray	100	10	10
31DK80	56	42.5 x 48	0.70	50	Black	100	10	10
31DK36	56	42.5 x 48	0.70	50	Clear	100	10	10
5XL59	56	42.5 x 48	0.70	50	Gray	100	10	10
31DK51	56	42.5 x 48	1.00	65	White	100	10	10
31DK81	56	42.5 x 48	1.10	70	Black	100	10	10
31DK44	56	42.5 x 48	1.10	70	Clear	100	10	10
5XL60	56	42.5 x 48	1.10	75	Gray	100	10	10
15E460	56	43 x 48	1.20	85	Clear	100	10	10
4YPA9	56	42.5 x 48	1.50	90	Gray	100	20	5
4YPC1	56	42.5 x 48	2.00	110	Gray	100	10	10
31DK82	60	38 x 58	0.70	50	Black	100	10	10
31DK38	60	38 x 58	0.70	50	Clear	100	10	10
5XL65	60	38 x 58	0.90	60	Gray	100	10	10
31DK83	60	38 x 58	0.95	65	Black	100	10	10
31DK39	60	38 x 58	0.95	65	Clear	100	10	10
31DK52	60	38 x 58	1.00	65	White	100	10	10
5XL63	60	38 x 58	1.10	75	Gray	100	10	10
31DK84	60	38 x 58	1.20	75	Black	100	10	10
31DK45	60	38 x 58	1.20	75	Clear	100	10	10
4YPC2	60	38 x 58	1.50	90	Gray	100	20	5
31DK47	60	38 x 58	1.70	90	Clear	100	10	10
4YPC3	60	38 x 58	2.00	110	Gray	100	10	10

Call or visit your local branch or go to grainger.com/toughguy for complete product line information.

©2019 W.W. Grainger, Inc. W-BUPX115-01



GRAINGER.COM | 1.800.GRAINGER

