



# Swivel Outlet Flow Controls

Legris' swivel outlet flow controls are designed to allow a vertical or angled tube exit where access is restricted.

## Product Features:

- Glass-reinforced nylon 6.6 body
- Stainless steel gripping ring
- Nickel-plated brass adjustment screw
- Nickel-plated brass locking nut
- Nickel-plated brass threads
- Nitrile D-seal
- Silicone-Free

## Markets:

- Factory/Process Automation
- Life Science
- Food Processing
- Water and Beverage
- Petrochemical

## Applications:

- Packaging
- Filling
- Dispensing
- Bottling
- Pneumatic Circuits

## Specifications:

**Pressure Range** 14.5 to 145 psi (1 to 10 bar)

**Temperature Range** 32° to 158° F (0° to 70° C)

## Compatible Tubing:

- Semi-rigid nylon
- Polyurethane 95 Durometer Shore A
- Nylon
- Fluoropolymer

