

Previously known as: PowerFlex® 80-600



Cut



Heat



Heavy Duty

## Excellent cut resistance, with comfort & grip

- Ansell's ActivArmr 80-600 glove is to safely handling glass, metal and plastics. It offers exceptional cut resistance and robust overall mechanical performance plus superior comfort.
- ActivArmr 80-600 glove is rated at the exceptionally high cut level of EN level 4. This high level of protection is achieved through the Kevlar® knitted liner and natural rubber coating. This coating stands up very well to abrasion, tearing and punctures.
- The latex coating's raised crinkle finish gives the glove an excellent grip in both dry and wet conditions.



### Industries

- Metal fabrication

### Applications

- Forging operations
- Extruding, bending and punching shapes

Previously known as: PowerFlex®80-600

### Key Features

- The latex coating's raised crinkle finish gives the glove an excellent grip in both dry and wet conditions
- Available in a wide range of sizes to protect more workers
- Also available in vend pack

### Performance Standards & Regulatory Compliance

#### REACH Compliant



### Technologies



### Specifications

BRAND   STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLOR	PACKAGE
ActivArm® 80-600	<b>Finishing:</b> Palm Coated <b>Coating Material:</b> Natural Latex Rubber <b>Liner Material:</b> Kevlar® <b>Cuff Style:</b> Knitwrist	10	7, 8, 9, 10	250-280 mm/ 9.64-11.02in	Blue	<ul style="list-style-type: none"> <li>• 12 pairs in a bag</li> <li>• 72 pairs in a carton</li> </ul>

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
 Riverside Business Park  
 Blvd International, 55  
 1070 Brussels, Belgium  
 T: +32 (0) 2 528 74 00  
 F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
 111 Wood Avenue South,  
 Suite 210  
 Iselin, NJ 08830, USA  
 T: +1 800 800 0444  
 F: +1 800 800 0445

#### Australia

Ansell Limited  
 Level 3,678 Victoria Street,  
 Richmond, Vic, 3121  
 Australia  
 T: +61 1800 337 041  
 F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
 (Malaysia) Sdn Bhd  
 Prima 6, Prima Avenue  
 Block 3512, Jaijan Teknokrat 6  
 T: +603 8310 6688  
 F: +603 8310 6699

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
 Blvd. Bernardo Quintana No. 7001-C,  
 Q7001 Torre II,  
 Suites 1304, 1305 y 1306,  
 Col. Centro Sur, c.p. 76079  
 Queretaro, Qro. Mexico  
 T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada  
 105 Lauder  
 Cowansville, QC J2K 2K8  
 Canada  
 T: +1 800 363 8340  
 F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.