



**MCR  
SAFETY**

**N9677**

**Ninja**

**Cut Protection  
Specification Sheet**

**PRODUCT DESCRIPTION:**

MCR Safety Ninja® gloves are engineered to provide the highest level of innovation. Each of the offerings in the Ninja® series include a unique shell and polymer combination incorporating the latest in hand protection technology. Our Ninja® Glove Line offers the greatest assortment of dexterity, sense of touch, and protection. The Ninja® Force features a 13 gauge Dyneema®/synthetic shell with a gray PU coated palm and fingertips. Made with DSM certified Dyneema®.

**FEATURES:**

- 13 Gauge Dyneema®/ Synthetic Shell
- PU Palm and Fingertips Coated
- CE 4542, ANSI level 3: 1100 grams
- Point of Purchase Hang Tag

**APPLICATIONS:**

Automotive Assembly, Farming, Landscaping, Agriculture, Carpentry, Construction, Glass handling, Janitorial, Roofing, Sheet metal industry, Material Handling



**TECHNICAL DATA FOR: N9677**

<b>Series</b>	Ninja	<b>EN 388 : CE Score - Abrasion</b>	4
<b>Material Group</b>	Strings	<b>EN 388 : CE Score - Cut</b>	5
<b>Product Type</b>	Cut Protection	<b>EN 388 : CE Score - Tear</b>	4
<b>Glove Size</b>	Large	<b>EN 388 : CE Score - Puncture</b>	1
<b>Gauge</b>	13 Gauge	<b>ANSI Cut</b>	ANSI Cut A3
<b>Material</b>	Dyneema	<b>ANSI Puncture</b>	ANSI Puncture 3
		<b>ANSI Abrasion</b>	ANSI Abrasion 5

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: [www.mcrcsafety.com](http://www.mcrcsafety.com)

©2018 MCR Safety - All Rights Reserved



**MCR**  
SAFETY

# N9677

## Ninja

### Cut Protection Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
N9677L	Large	13.63	4.88	3.39	28.368 lb.	0.197
N9677M	Medium	13.00	4.56	3.35	25.920 lb.	0.180
N9677S	Small	12.60	4.24	3.35	23.328 lb.	0.162
N9677XL	X - Large	14.33	5.15	3.70	29.664 lb.	0.206
N9677XXL	XX - Large	15.08	5.43	3.86	32.256 lb.	0.224

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: [www.mcrcsafety.com](http://www.mcrcsafety.com)

©2018 MCR Safety - All Rights Reserved