

3M™ Speedglas™ Welding Helmet 9100 MP


To optimize the effective lifetime of your welding equipment and avoid the additional cost of replacement, regular maintenance is important. Replace all damaged parts immediately to help ensure intended degree of protection.

Before use

- **Helmet and headband.** Inspect for cracks or any damaged or defective parts. Replace if needed.
- **Protection plates.** To help provide the best possible vision, they should be clean and without scratches.
- **Face seal.** If the face seal is damaged, there is a risk that contaminated air will get inside the helmet. Verify it's in place and free from splits and tears.
- **Welding filter.** Ensure low battery indicator is not flashing and check that the sensors are clean and uncovered.
- **Breathing tube.** Confirm tube is not damaged or leaking any air. To extend the life of breathing tube, use a tube cover or a heavy-duty breathing tube.

After use

- **Clean the helmet.** Wipe with a moist tissue or cloth, both inside and outside the helmet. If you suspect that the inside of the breathing tube is dirty, it must be changed. DO NOT rinse, immerse in water, or clean with solvents.
- **Face seal and sweatband.** Remove for additional cleaning as needed and replace if they have splits or tears or whenever they become unhygienic.
- **Protection plates and visor plate.** Clean with a soft cloth and replace if any pits or scratches occur.
- **Breathing tube.** Replace if damaged, deformed or leaking any air.
- **Storage.** Store the helmet in a dry, clean area away from direct sunlight, high temperatures and solvents.



Part No	Description
Ⓜ-350	Versafo™ replacement head suspension (not shown).
Ⓜ-957	Versafo™ forehead comfort pad/sweat pad, 10/case.
Ⓜ-985	3M™ Peltor™ earmuff assembly kit.
04-0320-00	Battery, 2/case.
06-0000-10	Speedglas welding filter 9100V.
06-0000-20	Speedglas welding filter 9100X.
06-0000-30	Speedglas welding filter 9100XX.
06-0000-30*	Speedglas welding filter 9100XXi.
06-0200-10	Inside protection plate 9100V, 5/case.
06-0200-10-B	Part no 06-0200-10 (bulk), 25/case.
06-0200-20	Inside protection plate 9100X, 5/case.
06-0200-20-B	Part no 06-0200-20 (bulk), 25/case.
06-0200-30	Inside protection plate 9100XX, 5/case.
06-0200-30-B	Part no 06-0200-30 (bulk), 25/case.
06-0200-51	Outside protection plate standard, 10/case.
06-0200-51-B	Part no 06-0200-51 (bulk), 50/case.
06-0200-52	Outside protection plate scratch resistant, 10/case.
06-0200-52-B	Part no 06-0200-52 (bulk), 50/case.
06-0200-53	Outside protection plate high temperature, 10/case.
06-0200-53-B	Part no 06-0200-53 (bulk), 50/case.
06-0400-54	Headband back part.
06-0400-54-B	Part no 06-0400-54 (bulk), 5/case.
06-0400-55	Battery holder 9100, 2/case.
06-0400-55-B	Part no 06-0400-55 (bulk), 10/case.
06-0500-56	Magnification plate 1.5x.
06-0500-57	Magnification plate 2.0x.
06-0500-58	Magnification plate 2.5x.
06-0500-59	Magnification plate 3.0x.
06-0700-51	Wide-view clear grinding visor, standard, 5/case.
06-0700-54	Wide-view clear grinding visor, anti-fog, 5/case.
06-0700-63	Front panel, chrome.
06-0700-64	Wide-view clear grinding visor frame, black.
06-0700-73	Side window cover plates, 2/case.
06-0700-74	Face seal.
06-0700-75	Welding helmet 9100 MP with hard hat, without welding filter.
06-0700-76	Pivot kit.
06-0700-77	Flip-up mechanism.
06-0700-78	Inner shield.
06-0700-79	Outer shield.
06-0700-80	Hard hat incl pivot kit.
06-0700-81	Radiant heat hard hat cover for 9100 MP helmet.
06-0700-82	Throat and neck coverage.

* The welding filter 9100XXi fits with all Speedglas welding helmet series 9100. However, the grind and memory features are not available when used in combination with the welding helmet 9100 MP. Also, tack mode is not available in the 9100XXi ADF model.

Further information and advice

To request a quote or place an order for spare parts, please contact your 3M approved distributor. Please note that higher than normal levels of pollutants, heat and sparks will require more frequent replacement of components. If you require additional guidance, please check the care and maintenance videos on our YouTube Channel (3M Speedglas) or contact your local 3M representative.

[youtube.com/3MSpeedglas](https://www.youtube.com/3MSpeedglas)

[facebook.com/3MSpeedglas](https://www.facebook.com/3MSpeedglas)

[instagram.com/3MSpeedglas](https://www.instagram.com/3MSpeedglas)

www.3M.com/Speedglas

3M, Speedglas, and Versafo are trademarks of 3M Company, used under license in Canada. Peltor is a trademark of 3M Svenska AB, used under license in Canada. For more information: Technical Assistance in US 1-800-243-4630. Technical Assistance in Canada 1-800-267-4414. © 3M 2015. All rights reserved.