



Cush-A-Claw[®]

Pipe & Conduit Support

Strut or Surface Mount to Meet All Your Tube, Pipe, or Hose Applications



- Easy Snap-in Installation of Tube, Pipe, or Hose
- Sure Grip Strut Base easily rotates into strut
- Will not rust
- Temperature range: -50°F to +275°F (-45°C to +135°C)

- Non-Conducting
- Saves Time and Money
- Works Great Indoors or Outdoors
- Seven Sizes of Tube and Three Sizes of EMT
- Designed for Light Duty Loads and Applications



Call ZSi-Foster at (800) 323-7053 or order now at zsi-foster.com

ZSi-Foster

Canton, MI | La Mirada, CA | Ocala, FL | Springfield, MO



Cush-A-Claw[®] Pipe & Conduit Support



Strut Mounted

Insert	Twist & Lock	Position Pipe	Snap In



Surface Mounted

Position	Mount w/Screw	Position Pipe	Snap In
Side grooves provide Centering guide		Counter-sunk hole allows tightening of any type of #10 fastener	

Strut Mounted

O.D. Tube Size			EMTS Conduit Sizes		
Part #	Size		Part #	Size	
	O.D.	In.		O.D.	In.
CL-04	1/4"	0.250	EMT-1/2	1/2"	0.706
CL-06	3/8"	0.375	EMT-3/4	3/4"	0.922
CL-08	1/2"	0.500	EMT-1	1"	1.163
CL-10	5/8"	0.625			
CL-12	3/4"	0.750			
CL-14	7/8"	0.875			
CL-18	1 1/8"	1.125			



Surface Mounted

O.D. Tube Size					EMTS Conduit Sizes				
Part #.	Size		Wt./100	Box Qty	Part #.	Size		Wt./100	Box Qty
	O.D.	In.				O.D.	In.		
CLS-04	1/4"	0.250	2.5	50	EMTS-1/2	1/2"	0.706	4.0	25
CLS-06	3/8"	0.375	3.0	50	EMTS-3/4	3/4"	0.922	5.0	25
CLS-08	1/2"	0.500	3.5	50	EMTS-1	1"	1.163	7.0	20
CLS-10	5/8"	0.625	4.0	25					
CLS-12	3/4"	0.750	4.5	25					
CLS-14	7/8"	0.875	4.5	25					
CLS-18	1 1/8"	1.125	7.0	20					



Call ZSi-Foster at (800) 323-7053 or order now at zsi-foster.com

ZSi-Foster - Canton, MI | La Mirada, CA | Ocala, FL | Springfield, MO