

PC 600 COLORS



ALL-PURPOSE GRADE, COLORED CLOTH DUCT TAPE

TYPICAL APPLICATIONS

- For general purpose use in industrial, plumbing, carpet, color-coding and splicing applications, as well as home and general repair applications, particularly where a discrete fix is needed

PRODUCT FEATURES

- Conformable
- Will not twist or curl during application
- Hand-tearable
- High tack

CONSTRUCTION

Overall Grade/Function: General purpose

Backing: Waterproof polyethylene film with a cloth carrier

Adhesive: Natural rubber

STANDARD WIDTH(S)

48 mm 72 mm

STANDARD LENGTH(S)

55 m

Contact your Shurtape sales representative for other available sizes

STORAGE AND USAGE CONDITIONS

Tape should be stored in its original packaging in a cool, dry area away from direct sunlight and should be used within 12 months of date of shipment. Surfaces to which tape is applied should be clean, dry and free of grease, oil or other contaminants.

COLOR(S)



PHYSICAL PROPERTIES

	STANDARD	METRIC
Tensile Strength	22 lbs/in width	38.5 N/10 mm
Adhesion to Stainless Steel	50 oz/in width	5.47 N/10 mm
Thickness	9 mils	0.23 mm
Elongation	16%	16%
Service Temperature Range	50 F to 200 F	10 C to 93 C

Physical and performance characteristics shown above are obtained from tests recommended by PSTC, ASTM, government agencies or Shurtape Technologies, LLC, Quality Assurance and Technical Service departments and do not represent a guarantee of product performance. Individual rolls may vary slightly from these averages. The user should determine whether the product is fit for a particular purpose and is suitable for the user's method of application before use.

