

PC 618 COLORS



PERFORMANCE GRADE, COLORED CLOTH DUCT TAPE



TYPICAL APPLICATIONS

- For holding, securing, seaming, repairing, bundling, splicing, packaging and masking in HVAC, industrial, commercial, utilities, trucking and automotive applications
- Can also be used as a condensation barrier in appliance assemblies

PRODUCT FEATURES

- Excellent tack, conformability and holding power
- Easy to unwind and tear

CONSTRUCTION

Overall Grade/Function: Performance
Backing: Waterproof polyethylene film with a cloth carrier
Adhesive: Natural rubber

STANDARD WIDTH(S)

48 mm 72 mm

STANDARD LENGTH(S)

55 m

Contact your Shurtape sales representative for other available sizes

APPLICABLE STANDARDS

Tested in accordance with UL 723; FSI 15/SDI 25; US Green Building Council – LEED® Point Contributor Product

STORAGE AND USAGE CONDITIONS

Tape should be stored in its original packaging in a cool, dry area away from direct sunlight and should be used within 12 months of date of shipment. Surfaces to which tape is applied should be clean, dry and free of grease, oil or other contaminants.

COLOR(S)



PHYSICAL PROPERTIES

	STANDARD	METRIC
Tensile Strength	27 lbs/in width	47.3 N/10 mm
Adhesion to Stainless Steel	55 oz/in width	6.02 N/10 mm
Thickness	10 mils	0.25 mm
Elongation	17%	17%
Service Temperature Range	50 F to 200 F	10 C to 93 C

Physical and performance characteristics shown above are obtained from tests recommended by PSTC, ASTM, government agencies or Shurtape Technologies, LLC, Quality Assurance and Technical Service departments and do not represent a guarantee of product performance. Individual rolls may vary slightly from these averages. The user should determine whether the product is fit for a particular purpose and is suitable for the user's method of application before use.

