



Available Colors: Burgundy, Brown, Slate Blue, Hunter Green, Charcoal



Portrait™ is intended for use in medium to heavy traffic areas. The stylish non-directional parquet design aggressively scrapes and cleans, while the rubber-edged perimeter entraps dirt and moisture for superior water and soil control. Molded rubber “cleats” on the underside of the mat grip the underlying surface minimizing mat movement.

Test	Test Description	*Results
ASTM D3884-01	Abrasion Resistance	0.6 grams (1.9%)
ASTM D6540-00	Accelerated Soiling	Based on Visual Inspection 3.5 - Vacuum Rating 4.0 - Rating After Extraction
ASTM E648-03	Critical Radiant Flux	0.15 Watts/Cm ²
CPSC FF 1-70 (ASTM D-2859)	Surface Flammability of Carpets and Rugs Ignition Characteristics - Finished Textile Floor Covering Material	Pass
-	Water Retention	Weight Gain = 44.6% (0.353 gals./yd ²)

*All testing of NoTrax® floor matting has been performed by an independent testing laboratory.

07/2014

Appearance Rating Key	
5	No change
4	Slight change
3	Noticeable change
2	Considerable change
1	Severe change

- 26 oz. face weight
- Thickness: 3/8"
- Rubber underside cleat design resists mat slippage
- Stock Sizes: 2' x 3', 3' x 4', 3' x 5', 3' x 10', 4' x 6', 4' x 10'
- Recommended and approved product as part of the GreenTRAX™ program for “Green Cleaning” environments

