



**MCR
SAFETY**

4620A

**Welder
Specification Sheet**

PRODUCT DESCRIPTION:

MCR Safety has the perfect welders glove to fit your individual needs. The 4620A Memphis welders glove features Premium quality cow side leather, Aluminized back, reinforced thumb and palm, wool lining, DuPont™ Kevlar® stitching, and a Wing thumb. It is lined with a cotton full sock jersey lining and has self hemmed cuffs.

FEATURES:

- Premium quality cow side leather
- Sewn with DuPont™ Kevlar® for durability
- Aluminized back
- Wool lining

APPLICATIONS:

Construction, Foundry, Heliarc, Iron work, Mig/Tig, Millwright operations, Ship building, Steel Work, Welding



TECHNICAL DATA FOR: 4620A

Material Group	Leather	Overall Length	14 in.
Product Type	Welder	ANSI Contact Heat	Level 3 (Applications less than 392 degrees F)
Glove Size	X - Large		
Material	Leather		
Leather Cut	Split Select Shoulder		
Leather Type	Cow Skin		
Grade	Premium		
Features	Sewn With KEVLAR		
Insulated	Insulated		
Lining	Wool		
Pattern	Gunn		
Thumb Style	Wing		
Thickness	1.1 - 1.6 mm		

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved



MCR
SAFETY

4620A

Welder
Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
4620A	X - Large	13.625	6.500	5.250	53.136 lb.	0.738

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved