



**MCR
SAFETY**

N9699 Ninja Dipped Specification Sheet

PRODUCT DESCRIPTION:

MCR Safety Ninja® gloves are engineered to provide the highest level of innovation. Each of the offerings in the Ninja® series include a unique shell and polymer combination incorporating the latest in hand protection technology. Our Ninja® Glove Line offers the greatest assortment of dexterity, sense of touch, and protection. The Ninja® HPT (Hydropellent Technology) features 15 gauge black nylon shell and a dark gray foam sponge coated palm and fingertips.

FEATURES:

- 15 Gauge Black Nylon Shell
- Black HPT Foam Coated Palm and Fingertips

APPLICATIONS:

Automotive Assembly, Farming, Landscaping, Material Handling, Warehousing



TECHNICAL DATA FOR: N9699

Series	Ninja	EN 388 : CE Score - Abrasion	4
Material Group	Strings	EN 388 : CE Score - Cut	1
Product Type	Dipped	EN 388 : CE Score - Tear	3
Glove Size	Large	EN 388 : CE Score - Puncture	1
Gauge	15 Gauge	ANSI Puncture	ANSI Puncture 2
Material	Nylon	ANSI Abrasion	ANSI Abrasion 3

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved



MCR
SAFETY

N9699

Ninja

Dipped

Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
N9699M	Medium	10.039	5.197	N/A	21.972 lb.	1.831
N9699XL	X - Large	10.827	6.063	N/A	25.932 lb.	2.161
N9699L	Large	10.425	5.866	N/A	23.400 lb.	1.950
N9699S	Small	9.646	4.920	N/A	20.592 lb.	1.716

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved