



MCR
SAFETY

9690Y

Flex Tuff

Dipped

Specification Sheet

PRODUCT DESCRIPTION:

Flex Therm options give you all of the benefits of our Flex Tuff series of gloves, but with the addition of Thermal protection! The 9690Y is made of a 100% high visibility acrylic string knit shell with a blue latex palm coating. With these gloves you can get a grip on being seen and staying warm!

FEATURES:

- Extra thermal protection
- High comfort level
- Allows manual dexterity
- For heavier duty requirements

APPLICATIONS:

Cold storage applications, Commercial fishing, Frozen food packaging, Airport , Carpentry, Construction, Flagman, HVAC, Janitorial , Material Handling, Plumbing



TECHNICAL DATA FOR: 9690Y

Series	Flex Tuff	EN 388 : CE Score - Abrasion	1
Material Group	Strings	EN 388 : CE Score - Cut	3
Product Type	Dipped	EN 388 : CE Score - Tear	3
Glove Size	Large	EN 388 : CE Score - Puncture	1
Gauge	7 Gauge	ANSI Cut	ANSI Cut A4
Material	Cotton / Polyester / Acrylic	ANSI Contact Heat	Level 4 (Applications less than 500 degrees F)
Insulated	Insulated		

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved



MCR
SAFETY

9690Y
Flex Tuff
Dipped
Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
9690YS	Small	10.31	5.92	3.62	19.818 lb.	3.303
9690YXL	X - Large	11.11	6.49	3.74	24.558 lb.	4.093
9690YM	Medium	10.55	6.10	3.62	21.150 lb.	3.525
9690YL	Large	10.79	6.25	3.62	23.280 lb.	3.880

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved