

# INSULATED 66 PIECE SET IN TOOL BOX



Tools that work for you

Insulated 66 Piece Tool Set Includes Screwdrivers, T-handles, Pliers & Cutters, Ruler, Knife Sockets & Accessories in Tool Box

**SKU: 32877**      **Grainger #: 26X240**

## Details

- Insulation 10,000 Volt Tested & 1000 Volt Rated
- Insulated Tools Individually Tested For Insulation Integrity
- Tool Box Included
- Professional Quality Tools - Made By Wiha

**Insulation Standards:** EN/IEC 60900, ASTM F-1505-10, VDE 0682/part 201, NFPA70E & CSA



## Pliers & Cutters

- 6.3" Long Nose Pliers
- 8.0" Long Nose Pliers
- 6.3" Long Flat Nose Pliers
- 6.3" Bent Nose Pliers
- 6.3" Stripping Pliers
- 8.0" Adjustable Wrench
- 9.0" Combo Pliers/Crimpers
- 6.3" Diagonal Cutters - Dynamic Joint
- 8.0" BiCut SuperCut Pliers - Dynamic Joint
- 6.3" Cable Cutters - Dynamic Joint

## Slotted Screwdrivers

- Insulated Slotted 2.0mm
- Insulated Slotted 2.5mm
- Insulated Slotted 3.0mm
- Insulated Slotted 3.5mm
- Insulated Slotted 4.0mm
- Insulated Slotted 4.5mm
- Insulated Slotted 5.5mm
- Insulated Slotted 6.0mm
- Insulated Slotted 6.5mm
- Insulated Slotted 8.0mm
- Insulated Slotted 10.0mm

## Phillips Screwdrivers

- Insulated Phillips #0
- Insulated Phillips #1
- Insulated Phillips #2
- Insulated Phillips #3

## Inch Nut Drivers

- Insulated Nut Driver 7/32"
- Insulated Nut Driver 1/4"
- Insulated Nut Driver 5/16"
- Insulated Nut Driver 3/8"
- Insulated Nut Driver 7/16"

## Metric Nut Drivers

- Insulated Nut Driver 5.0mm
- Insulated Nut Driver 5.5mm
- Insulated Nut Driver 6.0mm
- Insulated Nut Driver 7.0mm
- Insulated Nut Driver 8.0mm
- Insulated Nut Driver 10.0mm
- Insulated Nut Driver 13.0mm

## Hex Inch T-Handles

- Insulated T-handle Hex 5/32"
- Insulated T-handle Hex 3/16"
- Insulated T-handle Hex 7/32"
- Insulated T-handle Hex 1/4"
- Insulated T-handle Hex 5/16"
- Insulated T-handle Hex 3/8"

## Hex Metric T-Handles

- Insulated T-handle Hex 4.0mm
- Insulated T-handle Hex 5.0mm
- Insulated T-handle Hex 6.0mm
- Insulated T-handle Hex 8.0mm

## Torx Screwdrivers

- Insulated Torx T6
- Insulated Torx T7
- Insulated Torx T8
- Insulated Torx T9
- Insulated Torx T10
- Insulated Torx T15
- Insulated Torx T20
- Insulated Torx T25
- Insulated Torx T30

## Terminal Block Screwdrivers

- Insulated Sit/Ph Terminal #1
- Insulated Sit/Ph Terminal #2

Weight (lbs)	27.000
RoHS Compliant	Yes
Head Type	slotted, phillips, hex metric, hex inch, torx, square, terminal block, nut driver inch, nut driver metric
Pieces In Set	80
UPC	084705328775
UNSPSC	27111736

## Square Screwdrivers

- Insulated Square #1
- Insulated Square #2

## Inch Sockets

- Insulated Socket 1/2"
- Insulated Socket 9/16"
- Insulated Socket 5/8"
- Insulated Socket 11/16"
- Insulated Socket 3/4"
- Insulated Socket 13/16"
- Insulated Socket 7/8"

## Metric Sockets

- Insulated Socket 13mm
- Insulated Socket 14mm
- Insulated Socket 15mm
- Insulated Socket 17mm
- Insulated Socket 19mm
- Insulated Socket 20mm
- Insulated Socket 22mm

## Accessories

- Insulated Ratchet 3/8" Drive
- Insulated 4.9" Extension 3/8" Dr.
- Insulated L-key 10mm
- Insulated L-key 1/2"
- Insulated Cable Knife 50mm
- 2 Meter Ruler In/MM