



Technical Information Sheet



Compact Fluorescent Reflector
2CUV7-15CFLPAR30/LN/27 (4)

GENERAL CHARACTERISTICS

<u>Lamp Type</u>	Compact Fluorescent, Reflector
<u>Bulb Type</u>	N/A
<u>Base Type</u>	Standard (Medium) Screw E26
<u>Base Material</u>	Nickel Plated Brass
<u>Watts</u>	15
<u>Voltage</u>	120
<u>Incandescent Equivalent Wattage</u>	60
<u>Average Rated Hours</u>	10,000
<u>CFL Starting Temperature (Fahrenheit)</u>	5 Degrees F
<u>ANSI Code</u>	N/A
<u>Envelope Type</u>	Hard
<u>Burn Base up or down</u>	Universal
<u>Beam Angle</u>	110

PHOTOMETRIC CHARACTERISTICS

<u>Lumens (Initial)</u>	630
<u>Mean Lumens</u>	540
<u>Approx Lumens</u>	N/A
<u>Average Rated Wattage</u>	N/A
<u>Color Temperature Kelvin</u>	2,700
<u>Finish Energy Star 4.0</u>	Clear
<u>Color Rendering Index (CRI)</u>	80

APPROVALS

<u>FCC</u>	Yes
<u>UL</u>	Yes
<u>CUL</u>	Yes
<u>CSA</u>	N/A
<u>Energy Star</u>	No

DIMENSIONS

<u>Maximum Overall Length (in) (MOL)</u>	4 5/8"
--	--------

PRODUCT INFORMATION

<u>Product Code</u>	2CUV7
<u>Description</u>	15CFLPAR30/LN/27 (4)
<u>Package Type</u>	Box
<u>Individual Package Size (Box)</u>	1
<u>Inner Carton Lamp Quantity</u>	6
<u>Master Carton Lamp Quantity</u>	12