



## Main

Range of product	9080GCB
Product or component type	Circuit Protector
Trip Unit Type	Thermal-magnetic
Electrical Connection	Box lugs

## Complementary

Protection type	Overcurrent
Contact operation	Trip-free
Device application	Industrial application
Line Rated Current	3 A
Number of Poles	1P
Voltage Rating	250 V AC 65 V DC
Wire Size	AWG 16...AWG 10 copper
Wire stripping length	12.70 mm (0.5 in)
Terminal Tightening Torque	Control circuit 0.79 N.m (7 lbf.in) cage type connector
Terminal Rating	Factory wiring only
Operating Temperature	-30...60 °C (-22...140 °F)
Calibration Temperature	21 °C (70 °F)
Mounting support	9080GH track 35 mm DIN rail
Height	87.63 mm (3.45 in)
Width	80.01 mm (3.15 in)
Depth	12.70 mm (0.5 in)

## Environment

Product certifications	CE UL recognized E233026 CCN QVNU2 CSA file 025490 class 3211 07
Standards	UL 1077 CSA C22.2 No 235 DIN 57470

## Ordering and shipping details

Category	21703 - 9080 GCB
Discount Schedule	CP5
GTIN	00785901481034
Package weight(Lbs)	0.07 kg (0.16 lb(US))
Returnability	Yes
Country of origin	DE

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.

## Contractual warranty

Warranty	18 months
----------	-----------