

## Straight Blade Devices

20A, 125V, 2 Pole, 3 Wire Grounding

# HBL<sup>®</sup> Extra Heavy Duty MAX Specification Grade Duplex Receptacle

# HUBBELL

## Features

- Weather-resistance complies with national electrical code requirements
- Finder Groove Face
- One-piece brass integral ground strap
- Deep body design with circuit ID face

## Ordering Information

Description	Device Color	UPC Number	Catalog Number
Weather-Resistant, back and side wired	Brown	783585320557	HBL5362WR

## Listings

NEMA<sup>®</sup> WD-6 Compliant  
UL Listed to UL498 File No. E2186  
Certified to CSA 22.2, No. 42 File 285  
Fed. Spec. WC596

## Specifications


Face	Nylon
Base	PBT
By-Pass Power Contacts	.036" (.9) Brass
Clamp	Brass
Terminal Screws	Brass
Contacts	0.031" (0.8) Brass
Automatic Self-grounding Clip	Stainless steel
Mounting Screws	Stainless Steel

## Performance

Electrical	
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum
Mechanical	
Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#12-#10 AWG stranded or solid copper wire only
Terminal Identification	Terminals identified in accordance with UL 498 and CSA
Environmental	
Flammability	Top: UL 94V-2, Base: UL 94V-0
Operating Temperatures	Maximum continuous 75°C; minimum -40°C (w/o impact)



20A 125V  
NEMA 5-20R  
UL CSA  
1 HP



## Complementary Products

Wallplate or Weatherproof Cover

Duplex Opening

## Online Resources

Customer Sales Drawings  
eCatalog  
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

