

DeWALT
GUARANTEED TOUGH.

DCB102
JOB SITE CHARGING STATION

20v MAX*
LITHIUM ION

12v MAX*
LITHIUM ION



LED DIAGNOSTICS

communicates battery charge status: charged, charging, replace pack and battery too hot or too cold

CHARGES 12V-20V DeWALT BATTERIES
in 70 minutes or less

2 USB PORTS
to charge compatible devices
(1.5 A max output)

*Maximum initial battery voltage (measured without a workload) is 20 volts. Nominal voltage is 18.

3 YEAR <small>LIMITED WARRANTY</small>	1 YEAR <small>FREE SERVICE</small>	90 DAY <small>MONEY BACK GUARANTEE</small>
--	--	--

DEWALT®

20V MAX*/LITHIUM ION

SYSTEM



Dealer Stamp

1-800-4 DEWALT®

www.DEWALT.com

Copyright ©2015 DEWALT. The following are examples of trademarks for one or more DEWALT power tools and accessories: The yellow and black color scheme; the "D"-shaped air intake grill; the array of pyramids on the handgrip; the kit box configuration; and the array of lozenge-shaped humps on the surface of the tool.