



**'Cutting Edge' Solutions
for all types of
tubing material**

Copper & Aluminium Tubing

118 AUTOFEED™ 2-in-1 Midget Cutter

New!

The 118 Midget Cutter combined with the detachable Ratcheting Handle is the most effective solution for use in tight spaces where cutters cannot easily be rotated by hand.

The Ratcheting Handle is also compatible with the 101 Midget Cutter.



32573 118 AUTOFEED™ 2-in-1 Midget Cutter - 6-28 mm

32933 Ratchet Handle only

101 / 103 / 104 / 117 Midget Tubing Cutters

Easy-to-use, fast and compact tubing cutters for use in restricted spaces on small diameter tubes.



40617 101 - with spare wheel - 6-28 mm

32985 104 - 5-24 mm

32975 103 - 3-16 mm

97787 117 Quick-Feed - 5-24 mm

150-L Enclosed Feed Tubing Cutter

Cut copper and aluminum in just a few seconds.

Featuring X-CEL™ (spare cutter wheel in knob, pin for tool-less replacement of cutter wheel) and a fold-away reamer for instant reaming.



66737 150-L - 6-35 mm

127 Inner-Outer Reamer

Convenient tool for fast and efficient reaming of copper and aluminium tubes.



34965 127 Inner/Outer Reamer - 6-37 mm

151 and 152 Quick Acting Tubing Cutters

Quick Acting-mechanism for instant and precise adjustment to tube diameter.

X-CEL™ for speed, efficiency and heavy-duty use. Spare cutter wheel and fold-away reamer included.



31632 151 - 6-42 mm

31642 152 - 6-66 mm

10 / 15 / 20 Screw Feed Tubing Cutters

Durable tubing cutters with screw feeding mechanism for stable tracking and smooth cutting.

All models feature a fold-away reamer.



32910 10 - 3-25 mm

32920 15 - 5-28 mm

32930 20 - 16-54 mm

Plastic & Multilayer Tubing

New!



RC-2375

A truly compact solution for large capacity plastic and multilayer pipe allowing fast one-hand operation!

Features Quick-Ratcheting mechanism and the advanced X-CEL™ blade with teflon coating for greater performance and ease of cut.

30088 RC-2375 - 12-63 mm



RC-1625 Ratchet Cutter

Europe's new standard for cutting all types of plastic material and Multilayer.

The powerful X-CEL™ blade combined with Quick-Ratcheting mechanism, reduce time and required handforce on all plastic material.

23498 RC-1625 - 3 - 42 mm

New!



PC-1375 ML

Cuts plastic and multilayer tubes with just one single stroke!

Automatically adjusts to any tube size with its spring-loaded handle and features a detachable adapter for instant re-rounding of Multilayer tube.

23493 PC-1375 ML - 3-35 mm



PC-1250

Versatile Single Stroke cutter with a reversible blade equalling two times the blade life.

23488 PC-1250 - 3-42 mm



151-ML

Quick Acting Tubing Cutter specially designed for cutting Multilayer up to 50 mm. The professional's first choice for cutting Multilayer tubing!

66747 151-ML - 10-50 mm

Steel & Stainless Steel Tubing



35S

New!

Screw Feed cutter with six individual roller bearings for reduced friction and increased cutting speed on Stainless Steel.

The quick-change cutter wheel contains 2 side-bearings for minimized dragging and maximum cutting quality. Also features a spare cutter wheel in the ergonomic X-CEL™ knob.

29963 35S - 6-35 mm



65S

New!

A true expert in cutting large capacity Stainless Steel tube and pipe!

Offers all the X-CEL™ advantages and is unrivalled in cutting speed and quality with its Quick Acting and Spring Return features. Uses the same powerful cutter wheel as the 35S and contains a spare cutter wheel in the knob.

31803 65S - 6-65 mm



223S and 227S Stainless Steel Reamers

Premium reamers with hardened steel cone for inner reaming and outer deburring of Stainless Steel Tubes.

Both reamers feature an integrated measurement bar for easily measuring tube size.

29983 223S - 6-36 mm

29993 227S - 12-54 mm



151 CSST Cutter

New!

Finally a 'real' solution for cutting Corrugated Stainless Steel Tubes (CSST)!

This new Quick Acting CSST Cutter has special Split Floating guide wheels ensuring stable tracking in corrugations which results in high-quality cuts.

32078 151 CSST Cutter - 9½-25½ mm



Ridge Tool Europe
Interleuvenlaan 50
B-3001 Leuven
Belgium

Tel: +32 (0)16 380 280
Fax: +32 (0)16 380 381
ridgid.eu@emerson.com
www.ridgid.eu



RIDGID® operates a policy of continuous improvement and development and reserves the right to change design and specification of our products without notification or alteration of literature.

COMM INV - RID0027