

# HyFlex<sup>®</sup>

ADVANCED MECHANICAL PROTECTION

## 11-518

Ultra light weight cut protection with outstanding dexterity and maximum comfort



Cut



Light Duty

## Ultralight polyurethane gloves combining dexterity and advanced cut protection technology

- **Advanced design:** HyFlex<sup>®</sup> 11-518 industrial working gloves' ultralight seamless liner grants users an almost barehanded feel
- **Enhanced defenses:** Dyneema<sup>®</sup> Diamond Technology fiber guards against lacerations, achieving ISO B/ANSI A2 cut protection
- **Superior durability:** HyFlex<sup>®</sup> 11-518 PPE gloves possess EN and ANSI level 3 abrasion resistance, offering sustained personal protection
- **Supreme flexibility:** Their thin, flexible liner also ensures optimal dexterity and tactility in daily use
- **Genuine comfort:** D3 Pinky Knitting technology means the HyFlex<sup>®</sup> 11-518's form aligns with natural hand contours, for a more tailored fit



### Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Chemical
- Utilities
- Warehousing

### Applications

- Assembly & inspection of components
- Press injection molding
- Picking, fastening components
- Final assembly
- Delivery of parts to production line
- Applying finish to materials, products
- Handling incoming goods
- Opening furnaces draining pumps valves or lines and crackers BTX process

# HyFlex<sup>®</sup>

ADVANCED MECHANICAL PROTECTION

## 11-518

Ultra light weight cut protection with outstanding dexterity and maximum comfort

### Key Features

- Ultralight seamless liner: Safety gloves with a barehand feel
- Dyneema<sup>®</sup> Diamond Technology: Added cut protection
- Durable PU coating: EN and ANSI level 3 abrasion resistance

### Technologies



Fibre glass free

### Performance Standards & Regulatory Compliance

#### REACH Compliant



### Specifications

BRAND   STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLOR	PACKAGE
HyFlex <sup>®</sup> 11-518	<b>Finishing:</b> Palm Coated <b>Coating Material:</b> Polyurethane <b>Liner Material:</b> Nylon, Spandex, Dyneema <sup>®</sup> <b>Diamond Technology</b> <b>Cuff Style:</b> Knitwrist	18	6, 7, 8, 9, 10, 11	210-265 mm; 8.27-10.43 inches	Blue	<ul style="list-style-type: none"> <li>• 12 pairs in a bag; 12 bags in a carton</li> </ul>

### For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
 Riverside Business Park  
 Blvd International, 55  
 1070 Brussels, Belgium  
 T: +32 (0) 2 528 74 00  
 F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
 111 Wood Avenue South,  
 Suite 210  
 Iselin, NJ 08830, USA  
 T: +1 800 800 0444  
 F: +1 800 800 0445

#### Australia

Ansell Limited  
 Level 3,678 Victoria Street,  
 Richmond, Vic, 3121  
 Australia  
 T: +61 1800 337 041  
 F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
 (Malaysia) Sdn Bhd  
 Prima 6, Prima Avenue  
 Block 3512, Jaiin Teknokrat 6  
 T: +603 8310 6688  
 F: +603 8310 6699

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
 Blvd. Bernardo Quintana No. 7001-C,  
 Q7001 Torre II,  
 Suites 1304, 1305 y 1306,  
 Col. Centro Sur, c.p. 76079  
 Queretaro, Qro. Mexico  
 T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada  
 105 Lauder  
 Cowansville, QC J2K 2K8  
 Canada  
 T: +1 800 363 8340  
 F: +1 800 267 3551

Ansell, <sup>®</sup> and <sup>™</sup> are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

