

306C Pocket Digital Thermometer

Test the TPI advantage



Features:

- Field calibrateable to $\pm 2^{\circ}\text{F}$
- Easy-to-read LCD
- Data Hold for hard to reach areas
- Penetration tip
- Auto off
- 3-year limited warranty

APPLICATIONS:

HVACR

- Ambient Air
- Calibrate

Thermostats

- Vents
- Compressor Heads
- Registers

FOOD

- Grill & Surface Temperatures
- Serving Temperatures

ELECTRICAL

- Motor Temperatures
- Transformer Temperatures

Compact easy to use thermometer with large display and auto power off.



Comes with A306 protective boot



Specifications:	
Temperature Range	-58°F to 300°F
Accuracy	$\pm 2^{\circ}\text{F}$
Resolution	0.1°F
Sample Rate	1 reading every 1.5 second
Stem Length	4.9"
Tip Type	Penetration
Water Resistant	N/A
Water Proof	N/A
°C / °F Selectable	No
Data Hold	Yes
Auto Off	Yes
Battery Type	LR44