


M-4868 1



4.75 [120.7]
1.59 [40.4]
#20 AWG

CATALOG NO.	DESCRIPTION	COLOR
HBL1785	GRAY PLATE WITH 125 VOLT RED PILOT LIGHT	GRAY
HBL17CM85	YELLOW PLATE WITH 125 VOLT RED PILOT LIGHT	YELLOW

NOTES:

1. DIMENSIONS IN INCHES [MM]
2. .XX TOLERANCES TO BE ±.03

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
PLATE, PRESSWITCH	NEOPRENE	
PLATE	.062 STEEL	
PILOT LIGHT	1/2 W 125V	

SYM	REVISIONS	APP	DATE
1	REDRAWN ON CAD ON UPDATED FORMAT WITH CHANGES. ADDED TABLE, NOTES 1 & 2, AND DUAL DIMENSIONS, DECIMAL DIMS WERE FRACTIONAL, IN LIST OF PARTS ,ADDED 'PLATE, PRESSWITCH/NEOPRENE' REMOVED 'PAT. APPLIED FOR' FROM VIEW. DCN 13355 DCK	DJP	11/06

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
WEATHERPROOF PRESSWITCH
PLATE WITH RED PILOT LIGHT

TOLERANCES UNLESS OTHERWISE SPECIFIED FRACTIONS 1/64 DECIMALS ±.005 ANGLES ±2	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
	DR. BY GM	APP. BY DJP
	TR. BY DCK	SCALE FULL
	CHK'D BY DJP	DATE 11/1/06

DIMENSION SHEET FOR CAT. NO. M-4868
 REPAIRABLE NON-REPAIRABLE
 SEE TABLE
 B
 1