



M-3748 3



- NOTES:
1. WIRE CAPACITY: #16 AWG TO #12 AWG COPPER WIRE ONLY.
 2. CORD RANGE: Ø .32" TO .66", TYPE SJ, SJO, S OR SO.
 3. ALL DIMS. TO BE INCHES.
[mm]

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
COVER	ALUM.	POL. & LAC.
GLANDS	INSULPRENE	
CORD CLAMPS	STEEL	ZN. PLATE
CONTACTS	BRASS	
BLADE HOLDER	GLASS FILLED MELARINE	
SEALER KIT (NOT SHOWN)	EPOXY	

DIMENSION SHEET FOR CAT. NO. HBL24312

SYM	REVISIONS	APPD	DATE
3	ADDED NOTES 1 THRU 3; "HBL24312" WAS "24312"; REVISED TITLE: CONVERTED ALL DIMS. TO DECIMAL & METRIC PER DCN 11902 RCM	JPP	1/31/05

SYM	REVISIONS	APPD	DATE

20A 125V EXPLOSION PROOF
HUBBELLOCK PLUG

TOLERANCES UNLESS OTHERWISE SPECIFIED FRACTIONS ± 1/64 DECIMALS ± .005 ANGLES ± 2°	HARVEY HUBBELL, INC. BRIDGEPORT, CONN.	
	DR. BY <u>A.W.F.</u>	APP. BY _____
	TR. BY _____	SCALE <u>FULL</u>
	CHK'D. BY <u>JFH</u>	DATE <u>3-6-61</u>

M-3748

3