



M-5433 1



Ø .265 [6.7] 4 HOLES

- NOTES:
1. WIRE CAPACITY: #6AWG TO #2AWG, SOLID OR STRANDED COPPER WIRE ONLY.
 2. ALL DIMS. TO BE INCHES. [mm]

| LIST OF PARTS | | |
|-----------------|---------------|------------|
| DESCRIPTION | MATERIAL | FINISH |
| INSULATORS | DUREZ | BLACK |
| CONTACT SPRINGS | .040 COPPER | |
| GR. SHUNT | .020 BRASS | |
| CLAMPS | ALUMINUM | I-GREEN |
| CENTER POST | STEEL | ZINC PL. |
| AUX. SPRING | .020 BRONZE | |
| COIL SPRING | .055 ST. WIRE | COPPER PL. |
| CASING | .025 BRASS | ZINC PL. |
| COVER | CAST ALUM | GRAY |

| SYM | REVISIONS | APP | DATE |
|-----|--|-----|---------|
| 1 | ADDED NOTES 1&2; "HBL25503" WAS "25503"; CONVERTED ALL DIMS. TO DECIMAL & METRIC PER DCN 11902 RCM | JPP | 1/28/05 |

DIMENSION SHEET FOR CAT. NO. HBL25503
 REPAIRABLE NON-REPAIRABLE

B

M-5433

1

TITLE
 50A 250VAC, 2 POLE, 3 WIRE
 MOBILE X-RAY HUBBELLOCK OUTLET
 GROUNDED

| | | | |
|---------------------------------------|--|----------------------|--------------------|
| TOLERANCES UNLESS OTHERWISE SPECIFIED | | HARVEY HUBBELL, INC. | |
| FRACTIONS ± 1/64 | | BRIDGEPORT, CONN. | |
| DECIMALS ± .005 | | DR. BY <u>ASM</u> | APP. BY _____ |
| ANGLES ± 2° | | TR. BY _____ | SCALE <u>HALF</u> |
| | | CHK'D BY _____ | DATE <u>2-8-72</u> |