



M-4433 6



LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
INSULATORS	DUREZ	BLACK
BUSHING	RUBBER	
RETAINER COVER	LEXAN	YELLOW
GROUND SHUNT	020 BRASS	
COVER	062 STEEL	ZINC PL.
CORD CLAMPS	078 C.R.S.	YEL. NYLON COATING
CONTACTS	BRASS	
CLAMPS	ALUMINUM	WHITE
CLAMP SCREWS	STEEL	ZINC PL.

DIMENSION SHEET FOR CAT. NO. 26419

REPAIRABLE NON-REPAIRABLE

6	ADDED NOTES 1 THRU 3; "HBL26419" WAS "26419". REVISED TITLE; REMOVED "RUBBER GRIP" & "CORD GRIP" CALL-OUTS; CONVERTED ALL DIMS. TO DECIMAL/METRIC PER DCN 11902 RCM	JPP	1/27/05
SYM	REVISIONS	APP	DATE

B M-4433

- NOTES:
1. WIRE CAPACITY: #8/4 AWG TO #4/4 AWG COPPER WIRE ONLY.
 2. CORD RANGE: Ø .92 TO 1.45, TYPE "S" OR "SO".
[23.4] [36.8]
 3. ALL DIMENSIONS TO BE INCHES.
[mm]

TITLE
60A 600VAC, 3 POLE, 4 WIRE
GROUNDING HUBBELLOCK PLUG

TOLERANCES UNLESS OTHERWISE SPECIFIED		HARVEY HUBBELL, INC.	
		BRIDGEPORT, CONN.	
FRACTIONS ± 1/64	DR. BY <u>D.J.R.</u>	APP. BY _____	
DECIMALS ± .005	TR. BY _____	SCALE <u>FULL</u>	
ANGLES ± 2°	CHK'D. BY <u>J.C.H.</u>	DATE <u>3-2-66</u>	