

SHOWA
910

Top-of-the-line stainless steel fiber and a specialized wrapping process are combined to craft SHOWA 910.

[**FEATURES**

- 10-gauge stainless cut-resistant knit with steel engineered fiber
- Uncoated
- Ambidextrous
- Fully launderable

[**BENEFITS**

- Level A6 ANSI cut-resistance
- Superior cut protection with a special wrapping process

[**INDUSTRY**



Aerospace



Automotive



Manufacturing



Mechanical



Metallurgy



Municipal Services



Utilities



Warehousing and Distribution

[**IDEAL APPLICATIONS**

- Intricate parts handling
- Automotive repairs and maintenance
- Light assembly of oil-coated pieces
- Metal Stamping
- Painting and spray workshops
- Component Assembly
- HVAC
- Public utility
- Shipping/Receiving



TAA PRODUCTS

MADE IN USA

MATERIAL

- Glass Fiber
- HPPE
- Seamless knit
- Stainless steel

COATING

- Uncoated

GRIP

- N/A

STANDARDS



SHOWA 910



PACKAGING

- 12 Pair per polybag
- 72 Polybags per case
- 144 Gloves per case



SIZES

- XS
- S
- M
- L
- XL
- XXL



COLOUR

- White



[USER INSTRUCTIONS

Do not use where there are chemical, electrical, thermal or entanglement risks. Wash at 40°C max. Performance levels as per standard EN388 retained after 3 washes, subject to variations linked to actual usage conditions. The performance levels apply to the coated surface only. Store in a dry place, away from the light.

[DISCLAIMER

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment. The manufacturer reserves the right to make any modifications it deems necessary.

Get in touch

SHOWA USA | 579 Edison Street - Menlo, GA 30731, USA

USA@SHOWAgroup.com

© SHOWA Group 2018 | All rights reserved