



**MCR
SAFETY**

9680 Flex Tuff Dipped Specification Sheet

PRODUCT DESCRIPTION:

Our top selling FlexTuff® styles are manufactured on seamless knit liners that are flat dipped to reproduce the natural curved shape of the hand. As a result, workers benefit from less hand fatigue and greater productivity while performing detailed tasks to heavy duty jobs. The FlexTuff®'s strong 50% cotton/50% polyester shell and crinkle finish blue latex coating provides excellent protection in many applications.

FEATURES:

- Improves grip
- Natural rubber provides abrasion resistance
- Excellent comfort and fit
- Textured palm dip for extra grip and durability

APPLICATIONS:

Automotive Assembly, Farming, Landscaping, Material Handling



TECHNICAL DATA FOR: 9680

Series	Flex Tuff	EN 388 : CE Score - Abrasion	3
Material Group	Strings	EN 388 : CE Score - Cut	1
Product Type	Dipped	EN 388 : CE Score - Tear	4
Glove Size	Large	EN 388 : CE Score - Puncture	3
Gauge	10 Gauge	ANSI Cut	ANSI Cut A2
Material	Cotton Polyester Blend	ANSI Abrasion	ANSI Abrasion 4

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved



MCR
SAFETY

9680
Flex Tuff
Dipped
Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
9680L	Large	10.04	5.79	3.62	39.672 lb.	3.306
9680M	Medium	9.45	5.32	3.15	34.584 lb.	2.882
9680S	Small	8.66	4.72	2.95	31.704 lb.	2.642
9680XL	X - Large	10.62	5.60	3.54	44.256 lb.	3.688

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved