

RIDGID®

460 TRISTAND®



Portable TRISTAND® Chain Vice

Stand up to tough welding, threading and grooving demands!

The Ridge Tool Company has new portable chain vice stands for up to 12" diameter pipe. These versatile stands are designed to meet your rugged jobsite needs year after year.

Portable 460-6 TRISTAND Chain Vice

- **Optimised Base For More Working Area** – Benders are located at the rear of the base which provides 40% more working surface and three tool hangers are provided.
- **Integrated Ground Lug** – Provides a conductive surface to connect the weld ground.
- **Self Hooking for 4" Pipe** – No need to use a second hand to engage the chain into the wear plate.
- **Leg Chain** – Retains legs even when subjected to rugged use during operation and transport.
- **Rugged Tool Tray** – Prolonged stability before requiring a leg adjustment.

The 460-12 has all the features of the 460-6 model Plus:





- **12" Jaws & Extended Chain** – Grip up to 1/8" - 12" pipe.
- **Adjustable Rear Leg** – Provides the ability to level the stand.



ORDERING INFORMATION

Catalog No.	Model No.	Description	Pipe Capacity		Weight	
			in.	mm	lb.	kg
36273	460-6	Portable TRISTAND Chain Vice	1/8-6	6-150	47	21
36278	460-12	Portable TRISTAND Chain Vice	1/8-12	6-300	71	32

WHICH STAND IS RIGHT FOR YOU?

Model No.	425	40A	460-6	460-12
				
Cat. No.	16703	40130	36273	36278
Capacity	1/8–2 1/2	1/8–2 1/2	1/8-6	1/8–12
Shipping Weight kg (lbs.)	14.5 (32)	22 (48.5)	21 (47)	32 (71)
Vice Type	Chain	Yoke	Chain	Chain
Number of Tool Hangers	2	2	3	3
Leg Locking	Self Locking Latch	Over Center Tool Tray	Over Center Tool Tray	Over Center Tool Tray
Working Area (cm²)	80	436	648	623
Surface Area (cm²)	145	670	806	775



For the complete selection of the Ridge Tool product line, please refer to the Ridge Tool Catalog or www.RIDGID.eu

DISTRIBUTOR