



Cut



Medium Duty

This industrial sleeve offers best-in-class protection with unmatched comfort

- INTERCEPT™ Seamless High Performance Polyethylene (HPPE) With thumb slot
- This industrial sleeve with INTERCEPT™ Cut Resistance Technology provides best-in-class cut protection and a soft and cool feel to the worker
- The seamless design and the options of lengths and widths ensure an excellent fit and makes it the n°1 choice for all day comfort
- The HyFlex® 11-251 INTERCEPT™ industrial sleeves are engineered to perform in combination with any HyFlex® cut resistant glove
- Red and black over edge is to indicate wide (black) and narrow (red) for easy laundry sorting purpose



Industries

- Automotive
- Automotive Aftermarket
- Machinery and Equipment
- Metal fabrication

Applications

- Press shop operations
- Handling metal sheets & panels
- Handling parts with sharp, rough edges
- Handling structural and body components
- Inspection, selecting, checking parts
- Glass repair and replacement
- Seizing structural and body parts
- Body Surface checking, marking and touching up
- Adjusting systems and screwing
- Adjusting panels parts components

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-251

The most comfortable sleeve with Intercept technology

Key Features

- HyFlex® 11-251 with thumb slot come in different lengths and widths for optimal fit and comfort to fit every worker in the best possible way. Color-coding will help for easy sorting after laundry
- 11-251 INTERCEPT™ sleeves are made of black yarn and are silicone free for friendly paint and finish process
- The special knitted bicep cuffs keep the sleeve in place
- Compliant with FDA food handling regulations 21 CFR 177.1520 and 21 CFR 177.2600

Performance Standards & Regulatory Compliance

REACH Compliant



Technologies



INTERCEPT™
Cut Resistance Technology

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	PACKAGE
HyFlex® 11-251	Liner Material: Ansell INTERCEPT™ Technology Cuff Style: Knitwrist with thumb slot	15	Narrow, Wide, Extra Wide	12" (30 cm), 16" (40 cm), 18" (45 cm)	• 50 sleeves per box

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jaijan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

