



Elastic cuff for a comfortable fit

13-gauge HPPE and fiberglass blend shell provides industry-leading cut resistance

Back-of-hand IR-X® Impact Exoskeleton™ with high-flex design provides ANSI/ISEA 138 Level 2 protection on knuckles and Level 1 protection on fingers

Sandy nitrile palm coating provides superior grip and abrasion resistance

Reinforced thumb crotch patch

High dexterity



Launderable

2090X Thin Lizzie™

PROTECTION ZONES:

	Impact Protection		HPPE Blend Shell
	ANSI/ISEA CUT A4	GRAM SCORE 2053	UK CA CE 4 4X44EP
	ANSI/ISEA 138 1	ANSI/ISEA PUNCTURE 5	

FEATURES:

The Rig Lizard® Series is purpose-built to provide maximum grip in tough situations – with over five grip options for water, oils, muds, and lubricants. Each glove is also equipped with our highly flexible IR-X® Impact Exoskeleton™, keeping hands protected from smash and pinch injuries. This combination of multiple technologies and features makes the Rig Lizard® the ideal solution for common oil, gas, and mining hazards. And with options for cold weather protection, your hands can stay safe and comfortable in any environment.

ATTRIBUTES:

Style:	Seamless Coated
Grip:	Wet or dry
Cuff Style:	Elastic
Sizes:	5/XXS through 12/3XL

HexArmor®

Call **1-877-MY ARMOR** or visit **hexarmor.com**

HexArmor® products are cut and puncture resistant, NOT CUT AND PUNCTURE PROOF. Do not use with moving or serrated blades or tools. User shall be exclusively responsible to assess the suitability of the product as specified for any individual application or use. Protection zones are to be used as a general guide. Actual product protection zones may differ. Product features, design, protection zones subject to change.

Protected by U.S. Patent No. D703,389