



**'Cutting Edge' Solutions  
for all types of  
tubing material**

# Copper & Aluminium Tubing

## 118 AUTOFEED™ 2-in-1 Midget Cutter

**New!**

*The 118 Midget Cutter combined with the detachable Ratcheting Handle is the most effective solution for use in tight spaces where cutters cannot easily be rotated by hand.*

The Ratcheting Handle is also compatible with the 101 Midget Cutter.



32573 118 AUTOFEED™ 2-in-1 Midget Cutter - 6-28 mm

32933 Ratchet Handle only

## 101 / 103 / 104 / 117 Midget Tubing Cutters

*Easy-to-use, fast and compact tubing cutters for use in restricted spaces on small diameter tubes.*



40617 101 - with spare wheel - 6-28 mm

32985 104 - 5-24 mm

32975 103 - 3-16 mm

97787 117 Quick-Feed - 5-24 mm

## 150-L Enclosed Feed Tubing Cutter

*Cut copper and aluminum in just a few seconds.*

Featuring X-CEL™ (spare cutter wheel in knob, pin for tool-less replacement of cutter wheel) and a fold-away reamer for instant reaming.



66737 150-L - 6-35 mm

## 127 Inner-Outer Reamer

*Convenient tool for fast and efficient reaming of copper and aluminium tubes.*



34965 127 Inner/Outer Reamer - 6-37 mm

## 151 and 152 Quick Acting Tubing Cutters

*Quick Acting-mechanism for instant and precise adjustment to tube diameter.*

X-CEL™ for speed, efficiency and heavy-duty use. Spare cutter wheel and fold-away reamer included.



31632 151 - 6-42 mm

31642 152 - 6-66 mm

## 10 / 15 / 20 Screw Feed Tubing Cutters

*Durable tubing cutters with screw feeding mechanism for stable tracking and smooth cutting.*

All models feature a fold-away reamer.



32910 10 - 3-25 mm

32920 15 - 5-28 mm

32930 20 - 16-54 mm

# Plastic & Multilayer Tubing

**New!**



## RC-2375

*A truly compact solution for large capacity plastic and multilayer pipe allowing fast one-hand operation!*

Features Quick-Ratcheting mechanism and the advanced X-CEL™ blade with teflon coating for greater performance and ease of cut.

30088 RC-2375 - 12-63 mm



## RC-1625 Ratchet Cutter

*Europe's new standard for cutting all types of plastic material and Multilayer.*

The powerful X-CEL™ blade combined with Quick-Ratcheting mechanism, reduce time and required handforce on all plastic material.

23498 RC-1625 - 3 - 42 mm

**New!**



## PC-1375 ML

*Cuts plastic and multilayer tubes with just one single stroke!*

Automatically adjusts to any tube size with its spring-loaded handle and features a detachable adapter for instant re-rounding of Multilayer tube.

23493 PC-1375 ML - 3-35 mm



## PC-1250

*Versatile Single Stroke cutter with a reversible blade equalling two times the blade life.*

23488 PC-1250 - 3-42 mm



## 151-ML

*Quick Acting Tubing Cutter specially designed for cutting Multilayer up to 50 mm. The professional's first choice for cutting Multilayer tubing!*

66747 151-ML - 10-50 mm

# Steel & Stainless Steel Tubing



## 35S

**New!**

**Screw Feed cutter with six individual roller bearings for reduced friction and increased cutting speed on Stainless Steel.**

The quick-change cutter wheel contains 2 side-bearings for minimized dragging and maximum cutting quality. Also features a spare cutter wheel in the ergonomic X-CEL™ knob.

29963 35S - 6-35 mm



## 65S

**New!**

**A true expert in cutting large capacity Stainless Steel tube and pipe!**

Offers all the X-CEL™ advantages and is unrivalled in cutting speed and quality with its Quick Acting and Spring Return features. Uses the same powerful cutter wheel as the 35S and contains a spare cutter wheel in the knob.

31803 65S - 6-65 mm



## 223S and 227S Stainless Steel Reamers

**Premium reamers with hardened steel cone for inner reaming and outer deburring of Stainless Steel Tubes.**

Both reamers feature an integrated measurement bar for easily measuring tube size.

29983 223S - 6-36 mm

29993 227S - 12-54 mm



## 151 CSST Cutter

**New!**

**Finally a 'real' solution for cutting Corrugated Stainless Steel Tubes (CSST)!**

This new Quick Acting CSST Cutter has special Split Floating guide wheels ensuring stable tracking in corrugations which results in high-quality cuts.

32078 151 CSST Cutter - 9½-25½ mm