



**MCR
SAFETY**

N96790

Ninja

Dipped

Specification Sheet

PRODUCT DESCRIPTION:

MCR Safety Ninja® gloves are engineered to provide the highest level of innovation. Each of the offerings in the Ninja® series include a unique shell and polymer combination incorporating the latest in hand protection technology. Our Ninja® Glove Line offers the greatest assortment of dexterity, sense of touch, and protection. This Ninja® BNF features a 15 gauge nylon/spandex shell with a breathable nitrile foam (BNF) coating on the palm and fingertips.

FEATURES:

- 15 gauge nylon/spandex shell
- Breathable Nitrile Foam (BNF) coating on palm and fingertips
- Great dexterity, flexibility, and movement
- Ergonomic design for minimum hand fatigue
- Excellent wet or dry grip, CE score 4141

APPLICATIONS:

Automotive Assembly, Farming, Landscaping, Manufacturing, Material Handling



TECHNICAL DATA FOR: N96790

Series	Ninja
Material Group	Strings
Product Type	Dipped
Glove Size	Large
Gauge	15 Gauge
Material	Nylon

EN 388 : CE Score - Abrasion	4
EN 388 : CE Score - Cut	1
EN 388 : CE Score - Tear	4
EN 388 : CE Score - Puncture	1
ANSI Puncture	ANSI Puncture 2
ANSI Abrasion	ANSI Abrasion 4




MCR
SAFETY

N96790

Ninja

Dipped

Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
N96790L	Large	10.039	5.039	2.756	19.128 lb.	1.594
N96790M	Medium	9.449	4.645	2.756	17.844 lb.	1.487
N96790S	Small	9.055	4.173	2.559	16.152 lb.	1.346
N96790XL	X - Large	10.433	5.158	2.953	19.224 lb.	1.602
N96790XS	X - Small	8.661	4.134	2.559	15.192 lb.	1.266
N96790XXL	XX - Large	10.827	5.355	3.071	21.156 lb.	1.763

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved