



**MCR
SAFETY**

N96970 Ninja Dipped Specification Sheet

PRODUCT DESCRIPTION:

MCR Safety Ninja® gloves are engineered to provide the highest level of innovation. Each of the offerings in the Ninja® series include a unique shell and polymer combination incorporating the latest in hand protection technology. Our Ninja® Glove Line offers the greatest assortment of dexterity, sense of touch, and protection. The Ninja® BNF features an 18 gauge red nylon/spandex shell and black BNF (breathable nitrile foam) coated palm and fingertips.

FEATURES:

- Ninja "BNF", Breathable Nitrile Foam
- Seamless 18 Gauge Nylon/Spandex Red Shell
- Black Nitrile Foam Palm & Fingers
- Great Comfort, Fit, and Dexterity

APPLICATIONS:

Automotive Assembly, Farming, Landscaping, Material Handling, Warehousing, Manufacturing



TECHNICAL DATA FOR: N96970

Series	Ninja	EN 388 : CE Score - Abrasion	4
Material Group	Strings	EN 388 : CE Score - Cut	1
Product Type	Dipped	EN 388 : CE Score - Tear	2
Glove Size	Large	EN 388 : CE Score - Puncture	1
Gauge	18 Gauge	ANSI Abrasion	ANSI Abrasion 4
Material	Nylon	ANSI Contact Heat	Level 2 (Applications less than 284 degrees F)

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved



MCR
SAFETY

N96970

Ninja

Dipped

Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
N96970L	Large	9.842	5.039	2.953	15.744 lb.	1.312
N96970M	Medium	9.253	4.567	2.953	15.060 lb.	1.255
N96970S	Small	8.662	4.330	2.756	13.716 lb.	1.143
N96970XL	X - Large	10.433	5.237	2.953	16.776 lb.	1.398
N96970XS	X - Small	8.268	4.134	2.756	12.516 lb.	1.043
N96970XXL	XX - Large	10.827	5.394	2.953	18.564 lb.	1.547

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved