

# HyFlex®

ADVANCED MECHANICAL PROTECTION

## 11-281

The most comfortable sleeve with INTERCEPT™ Technology



Cut



Medium Duty

## Superior protection with unmatched comfort

- **Best-in-class Cut Resistance Technology**  
INTERCEPT™ Cut Resistance Technology has been tested to perform at or exceed industry standards. This Ansell proprietary technology offers best-in-class cut protection and increased comfort.
- **Best-in-class Comfort**  
The seamless design and the width options make these HyFlex® sleeves the worker's best choice for all-day comfort.



### Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Automotive Aftermarket
- Food Processing
- Oil and gas
- Utilities
- Warehousing

### Applications

- Glass repair and replacement
- Handling metal sheets & panels

# HyFlex<sup>®</sup>

ADVANCED MECHANICAL PROTECTION

## 11-281

The most comfortable sleeve with INTERCEPT™ Technology

### Key Features

- INTERCEPT™ Cut Resistance Technology provides best-in-class cut protection and a soft and cool feel to the worker
- The seamless design and the options of lengths and widths ensure an excellent fit and makes it the No. 1 choice for all-day comfort
- The HyFlex<sup>®</sup> 11-280 & 11-281 INTERCEPT™ sleeves are engineered to perform in combination with any HyFlex<sup>®</sup> cut resistant glove
- Available in two versions: Wide & Narrow
- Compliant with FDA food handling regulations 21 CFR 177.1520 and 21 CFR 177.2600

### Performance Standards & Regulatory Compliance

#### REACH Compliant



### Specifications

BRAND   STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	PACKAGE
HyFlex <sup>®</sup> 11-281	<b>Liner Material:</b> Ansell INTERCEPT™ Technology <b>Cuff Style:</b> Knitwrist with thumbslot	15	Narrow, Wide	12" (30 CM), 16" (40 CM), 18" (45 CM), 22" (55 CM)	• 50 pieces per box

### Technologies



**INTERCEPT™**  
Cut Resistance Technology

### For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 210  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Australia

Ansell Limited  
Level 3,678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jaijan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

Ansell, <sup>®</sup> and <sup>™</sup> are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

