

PIG® 55-Gallon Open-Head Poly Drum Lid

DRM965 For 55 gal. Open-Head Steel & Poly Drums, Thumb Screws

Replaces waste drum lid to allow easy access without the hassle of bolts.

- Large 18" diameter opening allows fast and easy waste collection
- Thick-wall, 100% polyethylene construction resists UV rays, rust, corrosion and most chemicals
- Attaches securely to drum with thumb screws to replace open-head drum lid
- Hinged lid stays upright when open; closes easily to help reduce vapor emissions
- Multiple lid color options allow you to segregate drums
- Lockable to help prevent unauthorized access
- Use optional screens (DRM553, DRM554) for draining or filtering



Item#	Description	Dimensions	Weight
DRM965-YW	Yellow,	ext. dia. 24.5" x 11.25" H	10.52 lbs.
DRM965-RD	Red,	ext. dia. 24.5" x 11.25" H	10.52 lbs.
DRM965-BK	Black,	ext. dia. 24.5" x 11.25" H	10.52 lbs.

Metric Equivalent:

Item#	Description	Dimensions	Weight
DRM965-YW	Yellow,	ext. dia. 62.2cm x 28.6cm H	4.8 kg
DRM965-RD	Red,	ext. dia. 62.2cm x 28.6cm H	4.8 kg
DRM965-BK	Black,	ext. dia. 62.2cm x 28.6cm H	4.8 kg

Specifications

Style	Without Bungs
Use With	55 gal. Open-Head Steel & Poly Drums
Dimensions	ext. dia. 24.5" x 11.25" H

Drum Mounting	Thumb Screws
Drum Size	55 gal.
Drum Type	Steel Drum; Poly Drum
Sold as	1 per box
Weight	10.52 lbs.
# per Pallet	18
Composition	Polyethylene
Padlockable	Padlockable w/ .25" Shackle
UNSPSC	24112112
Pigalog® Page Number	<u>Page 308</u>

Metric Equivalent

Dimensions	ext. dia. 62.2cm x 28.6cm H
Weight	4.8 kg

Technical Information

Technical Documents

[LDPE Products](#)

Disclaimers

[Flammables Warning](#)

Not for use with flammables (f.p.<141°F/60.5°C).



One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com