

DEWALT®

GUARANTEED TOUGH.®

COMPATIBLE ON MOST DEWALT
20V/60V/120V MAX* TOOLS



FUEL GAUGE

DCB612

12 Ah / 240 Wh CAPACITY

LONG RUNTIME

BATTERY WARRANTY

3 YEAR	3 YEAR	90 DAY
LIMITED WARRANTY	FREE SERVICE	MONEY BACK GUARANTEE

PLUS



TOOL CONNECT™
TAG READY - TRACK THIS TOOL™
(TAG SOLD SEPARATELY)

CORD WRAP



DCB104

TOUGHSYSTEM™
COMPATIBILITY

SHORT CHARGE TIME

CHARGER WARRANTY

3 YEAR	1 YEAR	90 DAY
LIMITED WARRANTY	FREE SERVICE	MONEY BACK GUARANTEE

SPECIFICATIONS

Input	120V AC, 60 Hz
Output	8.0 Amps DC

*Maximum initial battery voltage (measured without a workload) is 12, 20 and 60 volts. Nominal voltage is 10.8, 18 and 54.

**FLEXVOLT® 20V/60V MAX* LITHIUM ION BATTERY
& MULTI-PORT SIMULTANEOUS FAST CHARGER**

DEWALT CHARGING SOLUTIONS



DCB115



DCB102



DCB1800



DCB118



DCB104



DCB120



DCB127



DCB201



DCB203



DCB230



DCB204



DCB205



DCB206



DCB606



DCB609



DCB612

20 MIN

30 MIN
(2 Batteries)

N/A

N/A

20 MIN
(4 Batteries)

30 MIN

35 MIN
(2 Batteries)

N/A

N/A

30 MIN
(4 Batteries)

22 MIN

30 MIN
(2 Batteries)

35 MIN
(4 Batteries)

22 MIN

22 MIN
(4 Batteries)

30 MIN

35 MIN
(2 Batteries)

45 MIN
(4 Batteries)

30 MIN

30 MIN
(4 Batteries)

45 MIN

60 MIN
(2 Batteries)

67 MIN
(4 Batteries)

45 MIN

30 MIN
(4 Batteries)

60 MIN

70 MIN
(2 Batteries)

90 MIN
(4 Batteries)

40 MIN

40 MIN
(4 Batteries)

75 MIN

95 MIN
(2 Batteries)

112 MIN
(4 Batteries)

50 MIN

50 MIN
(4 Batteries)

90 MIN

100 MIN
(2 Batteries)

170 MIN
(4 Batteries)

60 MIN

60 MIN
(4 Batteries)

90 MIN

100 MIN
(2 Batteries)

140 MIN
(4 Batteries)

60 MIN

60 MIN
(4 Batteries)

135 MIN

135 MIN
(2 Batteries)

230 MIN
(4 Batteries)

75 MIN

75 MIN
(4 Batteries)

170 MIN

190 MIN
(2 Batteries)

360 MIN
(4 Batteries)

100 MIN

100 MIN
(4 Batteries)

Dealer Stamp

1-800-4-DEWALT

www.DEWALT.com

Copyright ©2018 DEWALT. The following are examples of trademarks for one or more DEWALT power tools, accessories, anchors, and concrete adhesives: the yellow and black color scheme; the "D"-shaped air intake grill; the array of pyramids on the handgrip; the kit box configuration; and the array of lozenge-shaped humps on the surface of the tool.

ICDCB612104SS