

PRODUCT FACT SHEET

STREAMLIGHT JR F-STOPTM ALKALINE OR LITHIUM BATTERY-POWERED FLASHLIGHT

MARKET

APPLICATIONS: Premium Professional Light - Law Enforcement, Fire & Rescue, Automotive, Industrial,

Outdoor, Consumer

DESCRIPTION: Ultra-compact light weight 2AA flashlight features the latest in power LED technology and has Spot

to Flood technology! This new feature makes the light very versatile for every lighting need. With the Bezel forward (for Spot mode) the light has a piercing beam. When the bezel is slid backwards, the beam opens up into a smooth flood pattern for area lighting. Packaged with a black nylon

flapless holster.

CASE MATERIAL: Machined aluminum case with non-slip knurled grip. Available in black anodized finish.

DIMENSIONS: Length: 6.5 in. (16.51 cm)

Major Diameter: 1.12 in. (2.84 cm)

Body Diameter: 0.75 in. (1.90 cm)

WEIGHT: 4.4 oz (125 grams) with alkaline batteries (included with purchase).

LENS: Unbreakable polycarbonate lens.

LIGHT SOURCE: C4® LED technology, impervious to shock with a 50,000 hour lifetime.

LIGHT OUTPUT: SPOT - 5,600 candela peak beam intensity, 150m beam distance and 220 lumens measured system

output.

FLOOD - 360 candela peak beam intensity, 38m beam distance and 250 Lumens measured system

output.

ON/OFF: Push button tail switch - momentary or constant on operation.

RUN TIME: | 🕔 | 6 hours to 10% lumen output level with Alkaline cells, 10.0 hours with (L91) Lithium cells.

BATTERY: Two (2) "AA" size, Alkaline or Lithium batteries.

FEATURES: C4® LED technology for extreme brightness.

IPX4 rated for water resistant operation. All openings o-ring sealed.

1 meter impact resistance tested.

Solid state circuitry provides regulated light output throughout battery life.

Removable pocket clip.


APPROVALS: (Meets applicable European Community Directives.

WARRANTY: Streamlight's Limited Lifetime Warranty

OPTIONAL

ACCESSORIES: Rubber helmet strap, Magnetic clip holder

1	FL1 STANDARD	SPOT	FLOOD
OUTPUT	31/5	220 LUMENS	250 LUMENS
RUNTIME	0	6h	6h
DISTANCE		150m	38m
INTENSITY		5,600cd	360cd
,			



All performance claims to ANSI/PLATO FL1-2016 Standard

Issued: 10/06/2017 Revised: Rev: 0