

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-816

The ideal balance of comfort, tactility and durability



Multi Purpose



Light Duty

Unparalleled comfort. Free your hands to better perform.

- **You'll forget that you are wearing a glove**
Ultra-thin ergonomic design provides extreme tactility to handle small parts easily.
- **Skin Friendly Design**
Dermatologically tested, solventfree, and Oekotex certified for no harmful substances.
- **The performance you expect from a HyFlex!**
FORTIX™ Abrasion Resistance Technology delivers extended wear time for enhanced worker safety and productivity.



HyFlex®

ADVANCED MECHANICAL PROTECTION

11-816

The ideal balance of comfort, tactility and durability

Key Features

- Unparalleled comfort and extreme tactility**
 The combination between the thin liner and coating provide extreme comfort and a barehand feel for workers who rely on fingertip sensitivity for precision tasks
- Extended glove life and secure grip**
 The FORTIX™ coating lasts longer than comparable styles under abrasive conditions for a longer wear life. HyFlex 11-816 also ensures a secure grip in dry environments
- Silicone free**
 No transfer of silicone contaminants to metal parts prior to painting
- Clean & skin friendly**
 Benefits from proprietary washing process that efficiently extracts impurities to deliver a cleaner, more comfortable glove

Technologies



Performance Standards & Regulatory Compliance



0493



EN 388:2016



4121A



REACH Compliant

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLO R	PACKAGE
HyFlex® 11-816	Palm Coated, Foam Nitrile, Nylon, Spandex, Knitwrist	18	6, 7, 8, 9, 10, 11	219-261 mm; 8.6-10.2 inches	Black	• 12 pairs/bag, 12 bags/cart on



For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
 Riverside Business Park
 Blvd International, 55
 1070 Brussels, Belgium
 T: +32 (0) 2 528 74 00
 F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
 111 Wood Avenue South,
 Suite 210
 Iselin, NJ 08830, USA
 T: +1 800 800 0444
 F: +1 800 800 0445

Australia

Ansell Limited
 Level 3,678 Victoria Street,
 Richmond, Vic, 3121
 Australia
 T: +61 1800 337 041
 F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
 (Malaysia) Sdn Bhd
 Prima 6, Prima Avenue
 Block 3512, Jalan Teknokrat 6
 T: +603 8310 6688
 F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
 Blvd. Bernardo Quintana No. 7001-C,
 Q7001 Torre II,
 Suites 1304, 1305 y 1306,
 Col. Centro Sur, c.p. 76079
 Queretaro, Qro. Mexico
 T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
 105, rue Lauder
 Cowansville (Québec)
 J2K 2K8, Canada
 T: 1 800 363-8340
 F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2019 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

