



MCR
SAFETY

MG9694

Memphis

Dipped

Specification Sheet

PRODUCT DESCRIPTION:

These styles are well suited for Multi-Industrial applications that require high dexterity and comfort. The Memphis MG9694 features a seamless black 15 gauge nylon/spandex shell with a 3/4 dipped black bi-polymer coating. Then coated with nitrile dots on the palm and fingers for additional grip.

FEATURES:

- 15 Gauge nylon/spandex shell
- 3/4 dipped bi-polymer coating helps protect knuckles
- Nitrile dots on palm and fingers for extra grip and wear
- Excellent comfort and fit
- CE 4121

APPLICATIONS:

Automotive Assembly, Farming, Landscaping, Material Handling, Carpentry, Construction



TECHNICAL DATA FOR: MG9694

Series	Memphis	EN 388 : CE Score - Abrasion	4
Material Group	Strings	EN 388 : CE Score - Cut	1
Product Type	Dipped	EN 388 : CE Score - Tear	2
Glove Size	Large	EN 388 : CE Score - Puncture	1
Gauge	15 Gauge		
Material	Nylon		

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved



MCR
SAFETY

MG9694

Memphis

Dipped

Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
MG9694L	Large	9.645	5.433	2.362	23.112 lb.	1.926
MG9694M	Medium	9.251	4.882	2.362	21.072 lb.	1.756
MG9694S	Small	8.661	4.291	2.165	18.096 lb.	1.508
MG9694XL	X - Large	10.630	5.630	2.559	23.964 lb.	1.997
MG9694XS	X - Small	0	0	N/A	17.840 lb.	1.487

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved