

**3M** Science.  
Applied to Life.™

# Three duct tapes that can do it all

## 3M™ DT Series Duct Tapes

Tackle your everyday tasks with 3M™ DT Series duct tapes in three strengths. They resist curling, have a consistent unwind, and tear off the roll cleanly for the ultimate in ease of handling and application.

**Right performance. Right price.**



# Duct tape simplified



## 3M™ All Purpose Duct Tape DT8

*Conformable with instant bond*

Unique design offers high instant adhesion coupled with maximum conformability.

- Ideal for contoured surfaces and quick labeling
- Good tensile strength for light-duty bundling
- Use for poly abatement, quick repairs, splicing, temporary holding and fast attachments



## 3M™ Heavy Duty Duct Tape DT11

*Versatility with holding power*

Good holding power with a broad attribute performance make this the go-to choice.

- Sticks immediately and stays on irregular, hard-to-bond surfaces without lifting—even on most plastics
- Water-resistant polyethylene backing resists wear and light abrasion—good for securing temporary floor coverings
- Moisture-resistant seal in many containment situations, such as pipe sealing and attaching heavy poly draping
- Low-tack roll edges so rolls stay cleaner



## 3M™ Super Duty Duct Tape DT17

*Super thick for super tough jobs*

Ultra-thick, water-resistant backing resists wear and abrasion while still tearing easily by hand.

- Aggressive rubber adhesive grips instantly to a variety of surfaces including metal, glass, plastic and sealed concrete
- Excellent for repairing, seaming, extra-strength bundling and helps in protecting metal parts and surfaces against sandblast overspray
- Superior strength for the most demanding applications
- Low-tack roll edges so rolls stay cleaner

Description	Thickness	Roll Size	Color	UPC	Packaging	Case Qty
3M™ All Purpose Duct Tape DT8	8 mil	1.88" x 60 yds (48 mm x 54.8 m)	Silver	00-689330-17225-2	Individually wrapped	24
			Black	00-689330-17809-4		
3M™ Heavy Duty Duct Tape DT11	11 mil	1.88" x 60 yds (48 mm x 54.8 m)	Silver	00-689330-17227-6	Individually wrapped	24
			Black	00-689330-17228-3		
3M™ Super Duty Duct Tape DT17	17 mil	1.88" x 35 yds (48 mm x 32 m)	Black	00-689330-17229-0	Individually wrapped	24



**Closure and Masking Systems Division**  
**3M Center, Building 225-3S-06**  
**St. Paul, MN 55144-1000**

**Phone** 800-362-3550  
**Web** 3M.com/Masking

**Product Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

**Warranty, Limited Remedy and Disclaimer:** Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

3M is a trademark of 3M. © 3M 2021. All rights reserved. Please recycle. Printed in USA. 70-0710-0470-2 Rev 2/21