

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-812

Designed to easily tear apart at multiple high risks areas



Multi Purpose



Cut

Ergonomic Protection



Light Duty

Sacrifice your glove, nothing else!

- **Minimizes significantly the risk of severe injury if the glove becomes entangled in a rotating tool**
The only ultra-thin assembly glove designed to easily tear apart at multiple high risks areas.
- **Provides the tactility needed to grab even the smallest parts**
Ultra-thin liner delivers extreme tactility when high degree of precision is required.
- **Delivers the comfort your hands deserve!**
ZONZ Comfort Fit Technology offers extreme breathability to keep hands cool and comfortable.



Industries

- Machinery and Equipment
- Metal fabrication
- Automotive
- Automotive Aftermarket
- Chemical
- Utilities
- Warehousing

Applications

- Final assembly

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-812

Designed to easily tear apart at multiple high risks areas

Key Features

- **Easily tears at multiple risk areas**
Unique knitted design allows the glove to easily tear at multiple high risk areas, significantly reducing the risk of hand injury if the glove becomes entangled in a rotating tool
- **Ultra thin design**
Provides excellent tactility to grab even the smallest parts
- **ZONZ technology for enhanced comfort**
ZONZ technology offers extreme breathability to keep hands cool and comfortable

Usage Precautions

- This glove will not directly protect the worker from injuries caused by contact with a sharp or high-speed rotating machine.
- If a glove becomes entangled in a rotating machine, whether or not it tears, it should be discarded and not used again.
- HyFlex 11-812 has been designed for rotating tools having a minimum torque of 10 Nm [7.4 foot-pounds] and speeds over 200 rotations per minute (RPM). HyFlex 11-812 is not recommended for rotating tools with lower torques and/or speeds. An in-depth analysis of the application requirements through Ansell Guardian is essential before use.

Performance Standards & Regulatory Compliance

REACH Compliant



Technologies



ERGOFORM™

Ergonomic Design Technology



ZONZ™

Comfort Fit Technology

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLOR	PACKAGE
HyFlex® 11-812	Finishing: Palm Coated Coating Material: Foam Nitrile Liner Material: Nylon, Spandex Cuff Style: Knitwrist	18	6, 7, 8, 9, 10, 11	200-250 mm; 7.9-9.9 inches	White	12 pairs per bag; 12 bags per carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jaijan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

