



U-Bent Rapid Start T8

FB32T8/TL841/6 ALTO 20PK

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Warnings and Safety

• Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

Product data

| General Information | |
|------------------------------------|----------------------------------|
| Base | G13 [Medium Bi-Pin Fluorescent] |
| Life 3-Hr Start [Hrs] | 20000 h |
| Features | ALTO® (ALTO) |
| Light Technical | |
| Color Code | TL841 [CCT of 4100K (841)] |
| Initial lumen (Nom) | 2800 lm |
| Color Designation | TL841 |
| Design Mean Lumens | 2535 lm |
| Correlated Color Temperature (Nom) | 4100 K |
| Color Rendering Index (Nom) | 85 |
| Operating and Electrical | |
| Power (Rated) (Nom) | 32 W |
| Mechanical and Housing | |
| Cap-Base Information | Green Base |

| | |
|-----------------------|--|
| Nominal Length (Inch) | 22.44 |
| Bulb Shape | T8-6U [U-bent T 8/8 inch with 6" spacing] |

Approval and Application

| | |
|----------------------------|---------------|
| Energy Saving Product | Energy Saving |
| Picogram Per Lumen Hour | 59 pg/lm.h |
| Mercury (Hg) Content (Nom) | 3.0 mg |

Product Data

| | |
|---------------------------------|--------------------------|
| Order product name | FB32T8/TL841/6 ALTO 20PK |
| EAN/UPC - Product | 046677379025 |
| Order code | 379024 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 20 |
| Material Nr. (12NC) | 927860084102 |
| Net Weight (Piece) | 0.001 kg |

U-Bent Rapid Start T8

Dimensional drawing

Product

FB32T8/TL841/6 ALTO 20PK

FB32T8/6/841 22.44 ALTO ES

