



U-Bent Rapid Start T8

FB31T8/TL841/ALTO 15/1

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Warnings and Safety

• Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information		Nominal Length (Inch)	
Base	G13 [Medium Bi-Pin Fluorescent]		22.44
Life 3-Hr Start [Hrs]	24000 h	Bulb Shape	T8-1-5/8U [U-bent T 1inch with 1-5/8" leg spacing]
Features	ALTO® (ALTO)	Approval and Application	
Light Technical		Energy Saving Product	Energy Saving
Color Code	TL841 [CCT of 4100K (841)]	Mercury (Hg) Content (Nom)	3.0 mg
Initial lumen (Nom)	2750 lm	Product Data	
Design Mean Lumens	2430 lm	Order product name	FB31T8/TL841/ALTO 15/1
Correlated Color Temperature (Nom)	4100 K	EAN/UPC - Product	046677226749
Color Rendering Index (Nom)	85	Order code	226746
Operating and Electrical		Numerator - Quantity Per Pack	1
Power (Rated) (Nom)	31 W	Numerator - Packs per outer box	15
Mechanical and Housing		Material Nr. (12NC)	927861284101
Cap-Base Information	Green Base	Net Weight (Piece)	0.001 kg

U-Bent Rapid Start T8

Dimensional drawing

Product

FB31T8/TL841/ALTO 15/1

FB31T8/TL841 ALTO® ES

