



U-Bent Rapid Start T8

FB32T8/TL835/6 ALTO 20PK

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Warnings and Safety

• Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Base	G13 [Medium Bi-Pin Fluorescent]
Life 3-Hr Start [Hrs]	20000 h
Features	ALTO® (ALTO)
Light Technical	
Color Code	TL835 [CCT of 3500K (835)]
Initial lumen (Nom)	2800 lm
Color Designation	TL835
Design Mean Lumens	2535 lm
Correlated Color Temperature (Nom)	3500 K
Color Rendering Index (Nom)	85
Operating and Electrical	
Power (Rated) (Nom)	32 W
Mechanical and Housing	
Cap-Base Information	Green Base

Nominal Length (Inch)	22.44
Bulb Shape	T8-6U [U-bent T 8/8 inch with 6" spacing]
Approval and Application	
Energy Saving Product	Energy Saving
Picogram Per Lumen Hour	59 pg/lm.h
Mercury (Hg) Content (Nom)	3.0 mg
Product Data	
Order product name	FB32T8/TL835/6 ALTO 20PK
EAN/UPC - Product	046677379001
Order code	379008
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20
Material Nr. (12NC)	927860083502
Net Weight (Piece)	0.001 kg

U-Bent Rapid Start T8

Dimensional drawing

Product

FB32T8/TL835/6 ALTO 20PK

FB32T8/6/835 22.44 ALTO ES

