



High CRI T12

FB40/T12/CW Supreme/6 12PK

Philips T12 High CRI Lamps are energy-efficient lighting solutions and provide excellent color consistency over the life of the lamp.

Warnings and Safety

• Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Base	G13 [Medium Bi-Pin Fluorescent]
Life 3-Hr Start [Hrs]	18000 h
Light Technical	
Initial lumen (Nom)	2300 lm
Color Designation	Cool White Supreme
Design Mean Lumens	1955 lm
Correlated Color Temperature (Nom)	4100 K
Color Rendering Index (Nom)	90
Operating and Electrical	
Power (Rated) (Nom)	40 W
Mechanical and Housing	
Cap-Base Information	Aluminium [Aluminium Cap]
Nominal Length (Inch)	22.44

Bulb Shape	T12-6U [U-bent T 12/8 inch with 6" spacing]
Approval and Application	
Energy Saving Product	Not Applicable
Mercury (Hg) Content (Nom)	10.0 mg
Product Data	
Order product name	FB40/T12/CW Supreme/6 12PK
EAN/UPC - Product	046677423087
Order code	423087
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	927862003702
Net Weight (Piece)	0.001 kg

High CRI T12

Dimensional drawing

Product

FB40/T12/CW Supreme/6 12PK

FB40T12/6 CW Supreme

