

HELIX®

Knit wrist helps prevent dirt and debris from entering the glove

ProDerm certified

Ultimate dexterity and tactility

15-gauge Dyneema® Diamond shell provides lightweight, cool comfort

Flexible foam nitrile palm coating provides superior grip and abrasion resistance

Seamless construction for enhanced comfort and breathability

Silicone-free

Launderable for extended life



2066 Helix® Series

ATTRIBUTES:

Shell:	Dyneema® Diamond	
Coating:	Material:	Foam Nitrile
	Finish:	Smooth
	Weight:	Medium weight
	Breathability:	Very good
	Flexibility:	Very good
	Grip:	Dry, oil, or wet
Sizes:	6/XS through 11/XXL	

FEATURES:



In accordance with the criteria of Oeko-Tex® Standard 100 tested textiles guarantee that there are no substances that affect human health.



The safety gloves awarded this quality seal were clinically tested by the proDerm Institute for Applied Dermatological Research and are dermatologically approved.



REACH Compliant: Avoidance of substances classified as carcinogenic, mutagenic or reprotoxic, persistent, bioaccumulative or toxic.

PROTECTION ZONES:

	Dyneema® Diamond Shell		
	ANSI/ISEA CUT	GRAM SCORE	CE
	A3	1346	4X42C
	ANSI/ISEA PUNCTURE		
	3		



Call **1-877-MY ARMOR** or visit **hexarmor.com**

HexArmor® products are cut and puncture resistant, NOT CUT AND PUNCTURE PROOF. Do not use with moving or serrated blades or tools. User shall be exclusively responsible to assess the suitability of the product as specified for any individual application or use. Protection zones are to be used as a general guide. Actual product protection zones may differ. Product features, design, protection zones subject to change.

Engineered in Germany