



Cut



Medium Duty

## Resilient, cut-resistant polyurethane gloves, with dirt masking for long-lasting wear

- **Heightened resilience:** HyFlex® 11-751 PU-coated gloves demonstrate superior durability, achieving ANSI level 6 abrasion resistance
- **Advanced protection:** INTERCEPT™ Cut Resistance Technology yarn also grants them ISO C/ ANSI 4 cut resistance, making them safer and preventing workplace injuries
- **Considered aesthetics:** HyFlex® 11-751 industrial gloves have been designed with integrated dirt masking, for longer wear
- **Certified performance:** These safety gloves also comply with Centexbel standards EN420, for general requirements, and EN388, for mechanical hazards
- **Guaranteed convenience:** For added practicality, HyFlex 11-751 industrial working gloves are available in vend pack form, for easy access and re-application



### Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Automotive Aftermarket

### Applications

- General maintenance
- Hardware assembly
- Machining / Stamping / Cutting
- Raw material handling
- Seat and frame build

#### Key Features

- **Durable PU coating:** PPE gloves with ANSI level 6 abrasion defenses
- **INTERCEPT™ Cut Resistance:** Heightened protection from cuts
- **Dirt masking:** Stains and marks hidden in various applications

#### Performance Standards & Regulatory Compliance

##### REACH Compliant



#### Technologies



#### Specifications

BRAND   STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLOR	PACKAGE
HyFlex® 11-751	<b>Finishing:</b> Palm Coated <b>Coating Material:</b> Polyurethane <b>Liner Material:</b> HPPE, Fiber glass, Nylon, Spandex <b>Cuff Style:</b> Knitwrist	10	6, 7, 8, 9, 10	224-269mm, 8.81 - 10.59 inches	Black	<ul style="list-style-type: none"> <li>• 12 pairs in a bag; 12 bags in a carton</li> </ul>

#### For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

##### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
 Riverside Business Park  
 Blvd International, 55  
 1070 Brussels, Belgium  
 T: +32 (0) 2 528 74 00  
 F: +32 (0) 2 528 74 01

##### North America Region

Ansell Healthcare Products LLC  
 111 Wood Avenue South,  
 Suite 210  
 Iselin, NJ 08830, USA  
 T: +1 800 800 0444  
 F: +1 800 800 0445

##### Australia

Ansell Limited  
 Level 3,678 Victoria Street,  
 Richmond, Vic, 3121  
 Australia  
 T: +61 1800 337 041  
 F: +61 1800 803 578

##### Asia Pacific Region

Ansell Global Trading Center  
 (Malaysia) Sdn Bhd  
 Prima 6, Prima Avenue  
 Block 3512, Jaijan Teknokrat 6  
 T: +603 8310 6688  
 F: +603 8310 6699

##### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
 Blvd. Bernardo Quintana No. 7001-C,  
 Q7001 Torre II,  
 Suites 1304, 1305 y 1306,  
 Col. Centro Sur, c.p. 76079  
 Queretaro, Qro. Mexico  
 T: +52 442 248 1544 / 248 3133

##### Canada

Ansell Canada  
 105 Lauder  
 Cowansville, QC J2K 2K8  
 Canada  
 T: +1 800 363 8340  
 F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.