



**MCR
SAFETY**

N96780 Ninja Cut Protection Specification Sheet

PRODUCT DESCRIPTION:

MCR Safety Ninja® gloves are engineered to provide the highest level of innovation. Each of the offerings in the Ninja® series include a unique shell and polymer combination incorporating the latest in hand protection technology. Our Ninja® Glove Line offers the greatest assortment of dexterity, sense of touch, and protection. This Ninja® Wave features a 13 gauge Dyneema® Diamond Technology Shell with a black nitrile wave coating on the palm and fingertips.

FEATURES:

- 13 Gauge Dyneema® Diamond Technology Shell
- Black nitrile wave coating on the palm and fingertips
- Ergonomic design for minimum hand fatigue
- Excellent wet or dry grip

APPLICATIONS:

Automotive Assembly, Farming, Landscaping, Sheet metal industry, Material Handling, Construction, Glass handling, HVAC, Janitorial , Roofing



TECHNICAL DATA FOR: N96780

Series	Ninja	EN 388 : CE Score - Abrasion	4
Material Group	Supported	EN 388 : CE Score - Cut	4
Product Type	Cut Protection	EN 388 : CE Score - Tear	4
Glove Size	Large	EN 388 : CE Score - Puncture	4
Gauge	13 Gauge	ANSI Cut	ANSI Cut A3
Material	Dyneema	ANSI Puncture	ANSI Puncture 4
Features	Sold by pair	ANSI Abrasion	ANSI Abrasion 5

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved



MCR
SAFETY

N96780

Ninja

Cut Protection Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
N96780L	Large	10.237	5.355	N/A	38.016 lb.	0.264
N96780M	Medium	9.843	5.001	N/A	31.968 lb.	0.222
N96780S	Small	9.449	4.646	N/A	31.968 lb.	0.222
N96780XL	X - Large	10.630	5.394	N/A	40.032 lb.	0.278
N96780XXL	XX - Large	11.024	5.550	N/A	44.208 lb.	0.307

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved