

Locking Devices



30 Amp Plugs, Connectors Flanged Devices and Receptacles

30A 125/250V, 3Ø 250V AC, 3Ø 480V AC and 3Ø 600V AC Locking Devices,
3-Pole 3-Wire and 3-Pole 3-Wire and 3-Pole 4-Wire Grounding Inches (mm)

TECH-SPEC®



Rating	Poles/ Wires	Cord Diameter	Description	Tripple Gripper		Flanged Devices Equipment Base with Nylon White Cup		Weather Protective Power Inlets	Single Nylon Receptacle, All Black
				Nylon Plug	Nylon Connector	Male	Female	Die Cast Aluminum Plate*	
NEMA L10-30, 30A 125/250V AC Plug Connector	3-Pole 3-Wire	.300"-.950" (7.6-24.1)	Black/White	71030NP	71030NC	71030MB	71030ER	—	71030FR
NEMA L11-30, 30A 3Ø 250V AC Plug Connector	3-Pole 3-Wire	.300"-.950" (7.6-24.1)	Black/White	71130NP	71130NC	71130MB	71130ER	—	71130FR
NEMA L12-30, 30A 3Ø 480V AC Plug Connector	3-Pole 3-Wire	.300"-.950" (7.6-24.1)	Black/White	71230NP	71230NC	71230MB	71230ER	—	71230FR
NEMA L13-30, 30A 3Ø 600V AC Plug Connector	3-Pole 3-Wire	.300"-.950" (7.6-24.1)	Black/White	71330NP	71330NC	71330MB	71330ER	—	71330FR
NEMA L14-30, 30A 125/250V AC Plug Connector	3-Pole 4-Wire	.465"-1.150" (11.8-29.2)	Black/White Isolated Ground Orange	71430NP	71430NC	71430MB	71430ER	71430MBWP	71430FR 71430IG
NEMA L15-30, 30A 3Ø 250V AC Plug Connector	3-Pole 4-Wire	.465"-1.150" (11.8-29.2)	Black/White Isolated Ground Orange	71530NP	71530NC	71530MB	71530ER	71530MBWP	71530FR 71530IG
NEMA L16-30, 30A 3Ø 480V AC Plug Connector	3-Pole 4-Wire	.465"-1.150" (11.8-29.2)	Black/White	71630NP	71630NC	71630MB	71630ER	—	71630FR
NEMA L17-30, 30A 3Ø 600V AC Plug Connector	3-Pole 4-Wire	.465"-1.150" (11.8-29.2)	Black/White	71730NP	71730NC	71730MB	71730ER	—	71730FR

Note: *Supplied with gaskets, mounting screws and spring-loaded, self-closing lift cover.

See Section D for more information on isolated ground devices and Section J for more information on corrosion-resistant devices.

See page H-13 for 30 amp NEMA locking device dimensions..

See page H-20 for weather protective boots for 30 amp nylon locking plugs.