

Straight Blade Devices

15A, 125V, 2 Pole, 3 Wire Grounding

Bryant Hospital Grade Isolated Ground Receptacle



Features

- Triangle marking on face indicates isolated ground
- Slender/compact design
- Impact-resistant finder groove face
- Triple wipe contacts
- ID surface for marking identification of circuits

Ordering Information

Description	Color	UPC Number	Catalog Number
Hospital grade, isolated ground, finder groove face	Orange	781786005594	BRY8200IG

Listings

UL Listed to 498,	Complies with NEMA® WD-1 and WD-6 requirements
CSA Certified to C22.2, No. 42	Verified under Fed. Spec. WC596 (Standard only)

Specifications

Face	PBT
Base	PBT
Contacts	0.031" (0.8) Brass
Clamp	Nickel plated steel
Terminal Screws	Brass
Mounting Strap	Brass
Automatic Self-grounding Clip	Stainless steel
Mounting Screws	Stainless Steel

Performance


Electrical	
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum

Mechanical

Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14-#10 AWG copper stranded or solid conductor only
Terminal Identification	Terminals identified in accordance with UL 498 and CSA

Environmental

Flammability	UL 94V-2
Operating Temperatures	Maximum continuous 75°C; minimum -40°C (w/o impact)



A	4.06" (103.1)
B	3.28" (83.3)
C	1.65" (41.9)
D	2.75" (69.9)
E	1.30" (33.0)

Online Resources

eCatalog

Dimensions in Inches (mm)

Bryant Electric • An affiliate of Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484
Phone (800) 323-2792 • Specifications subject to change without notice